


D


C

B



A



RECEPTACLE CONNECTOR
INSERT:BLACK GLASS FILLED NYLON
94 V-O RATED
SHELL:STEEL PER ASTM A109
PLATED, .000200 MIN TIN
OVER .000100 MIN COPPER
UNDERPLATE.



SECTION D-D
SCALE 4:1



SECTION E-E
SCALE 4:1

- RECEPTACLE ACCEPTS SIZE 20 SOCKET CONTACTS (CONTACTS ORDERED SEPARATELY)
- 2 ALL PARTS SHIPPED UNASSEMBLED, EACH PART INDIVIDUALLY BULK PACKED.
- SHIELDS: MATERIAL-.020 THICK STEEL, PER ASTM A109, PLATED .000200 MIN TIN OVER .000100 MIN COPPER UNDERPLATE.
- RAISED CAVITY IDENTIFICATION AND AMP TRADEMARK.

1658646-1
PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.REITZEL 30JUL03	TE Connectivity				
DIMENSIONS: INCHES		CHK S.BOLASH 30JUL03					
		APVD M.WALMSLEY 30JUL03		NAME			
		PRODUCT SPEC 108-40030		KIT, RCPT, SHIELDING HARDWARE, SIZE 1, 9 POSITION, AMPLIMITE™ HDP-20			
MATERIAL SEE CALL OUT		FINISH SEE CALL OUT		SIZE A2	CAGE CODE 00779	DRAWING NO C-1658646	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 2:1	SHEET 1 of 1	REV P	