

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION, 19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
AF	50				J	REV PER 0710-0057-95	2/16/95	JR/JW

- 1 MATES WITH .032±.001×.187 TAB, PER NEMA DC-2
- 2 WIRE STRIP LENGTH .281
- 3 INSULATION SIZE .060-.135 DIA
- 4 DIMENSION DOES NOT INCLUDE TRIM BURR
- 5 .015 MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA



HOUSING: NYLON, COLOR-RED TRANSLUCENT RECEPTACLE: #3 HARD BRASS TIN PL .000080 MIN THK				2-520411-2	
MATERIAL & FINISH				PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± .015 ANGLES ± -	DR	10/31/88 P FORTNEY	AMP AMP INCORPORATED Harrisburg, Pa. 17105		
	CHK	11/4/88 MS FEHER			
	APPD	11/4/88 K RANDOLPH	NAME RECEPTACLE ASSY, ULTRA-FAST PLUS, LOOSE PIECE, .187 SERIES, 22-18 AWG		
	APPD	11/14/88 TL SHUTTER			
MATERIAL SEE TABLE	PRODUCT SPEC 108-2044		SIZE	FSCM NO	DRAWING NO
FINISH SEE TABLE	APPLICATION SPEC 114-2123		B	00779	520411
	WEIGHT -		SCALE	4:1	SHEET 1 OF 1