

Isolating plugs - P-DI GY - 3047390

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Isolating plugs, Length: 10.8 mm, Width: 3.5 mm, Height: 23.1 mm, Color: gray


The figure shows the orange version

Why buy this product

- Can be used in all ...-TG disconnect terminal blocks from the CLIPLINE complete system
- The P-DI isolating plug can be easily removed to release the connection and then "parked" back to front in the disconnect zone



Key commercial data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 140225
Weight per Piece (excluding packing)	0.63 g
Custom tariff number	85389099
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

General

Color	gray
Insulating material	PA
Inflammability class according to UL 94	V2

Dimensions

Width	3.5 mm
Length	10.8 mm
Height	23.1 mm

General

Maximum load current	20 A
----------------------	------

Isolating plugs - P-DI GY - 3047390

Technical data

General

	20 A
--	------

Classifications

eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127
eCl@ss 5.0	27141127
eCl@ss 5.1	27141111
eCl@ss 6.0	27141148
eCl@ss 7.0	27141148

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC002555
ETIM 5.0	EC002555

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

CSA / BV


Ex Approvals

Approvals submitted

Approval details

Isolating plugs - P-DI GY - 3047390

Approvals

CSA 	
Nominal current I _N	15 A

BV
