

## Interface module - UM 45-D50SUB/S/FRONT/Q - 2959654

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


VARIOFACE SLIM LINE, with screw connection and D-subminiature pin strip, for assembly at a right angle on NS 35/7.5, 50 positions



The illustration shows the version UM 25-D 9SUB/B/FRONT/Q



### Key commercial data

Packing unit	1 pc
GTIN	 4 017918 086305
Weight per Piece (excluding packing)	288.57 g
Custom tariff number	85369010
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Width	45 mm
Height	187 mm
Depth	45 mm

#### Ambient conditions

Ambient temperature (operation)	-10 °C ... 50 °C
Ambient temperature (storage/transport)	-10 °C ... 70 °C

#### General

Max. permissible operating voltage	125 V AC/DC
Max. perm. current (per branch)	2.5 A
	1 A (with even load on all branches)
Number of positions	50
Mounting position	any

# Interface module - UM 45-D50SUB/S/FRONT/Q - 2959654

## Technical data

### General

Degree of protection	IP20
Standards/regulations	DIN EN 50178
	IEC 60664
	IEC 62103
Rated insulation voltage	125 V
Rated surge voltage	1.2 kV (Functional insulation)
Pollution degree	2
Surge voltage category	II

### Connection data for connection 1

Connection name	PCB connection
Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3

### Connection data for connection 2

Connection name	D-SUB connection
Number of connections	1
Connection method	D-SUB pin strip
Number of positions	50

## Classifications

### eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

### ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604

# Interface module - UM 45-D50SUB/S/FRONT/Q - 2959654

## Classifications

### ETIM

ETIM 4.0	EC001604
ETIM 5.0	EC002780

### UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

## Approvals

### Approvals

---

#### Approvals

EAC

---

#### Ex Approvals

---

#### Approvals submitted

---

## Approval details

EAC
-----

## Accessories

### Accessories

#### System cable

Cable - CABLE-D50SUB/B/S/ 50/KONFEK/S - 2302269



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 0.5 m

## Interface module - UM 45-D50SUB/S/FRONT/Q - 2959654

### Accessories

Cable - CABLE-D50SUB/B/S/100/KONFEK/S - 2302272



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 1 m

---

Cable - CABLE-D50SUB/B/S/150/KONFEK/S - 2302285



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 1.5 m

---

Cable - CABLE-D50SUB/B/S/200/KONFEK/S - 2302298



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 2 m

---

Cable - CABLE-D50SUB/B/S/300/KONFEK/S - 2302308



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 3 m

---

Cable - CABLE-D50SUB/B/S/400/KONFEK/S - 2302311



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 4 m

---

## Interface module - UM 45-D50SUB/S/FRONT/Q - 2959654

### Accessories

Cable - CABLE-D50SUB/B/S/600/KONFEK/S - 2302324



Round shielded cable set, with 50-pos. D-SUB female and male connectors, cable length: 6 m

---

Cable - CABLE D-SUB-S/.../.../... - 2302340



Shielded round cable, assembled with one D-SUB male and one female connector, variable cable length

---

Cable - CABLE D-SUB-B-B-S/.../.../... - 2302421



Shielded round cable, assembled with two D-SUB female connectors, variable cable length

---

Cable - CABLE-D-50SUB/F/OE/0,25/S/0,5M - 2926292



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 0.5 m.

---

Cable - CABLE-D-50SUB/F/OE/0,25/S/1,0M - 2926302



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 1 m.

---

## Interface module - UM 45-D50SUB/S/FRONT/Q - 2959654

### Accessories

Cable - CABLE-D-50SUB/F/OE/0,25/S/1,5M - 2926315



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 1.5 m.

Cable - CABLE-D-50SUB/F/OE/0,25/S/2,0M - 2926328



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 2 m.

Cable - CABLE-D-50SUB/F/OE/0,25/S/3,0M - 2926331



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 3 m.

Cable - CABLE-D-50SUB/F/OE/0,25/S/4,0M - 2926344



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 4 m.

Cable - CABLE-D-50SUB/F/OE/0,25/S/6,0M - 2926357



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 6 m.

## Interface module - UM 45-D50SUB/S/FRONT/Q - 2959654

### Accessories

Cable - CABLE-D-50SUB-F-OE-0,25-S/... - 2900908



Shielded cable with a 50-pos. D-SUB female connector and one open end. The individual wires are labeled 1 to 50 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: variable.

### Drawings

Circuit diagram

