

**ARCA 302015**



Sample photo

**Order symbol:** ARCA 302015  
**Product nbr:** 8120002  
**Description:** Cabinet, PC  
**Remarks:** Grey cover, 1-point locking, hinges on the long side

**EAN:** 6418074079138  
**EI. number:**  
 Finland: 3423044  
 Denmark: 8212091003  
 Sweden: 2500110  
 Norway:

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key.  
 S versions with swinghandle 3-point locking system. F versions with flange opening. Door guide included.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		300	200	150	Ingress Protection (EN 60529): IP 66
<b>inch:</b>		11.8	7.9	5.9	Impact Resistance (EN 62262): IK 10 +35°C /IK 08 -25°C
Materials:					
<b>Material:</b>		Polycarbonate			
<b>Base colour:</b>		RAL 7035			
<b>Cover colour:</b>		RAL 7035			
<b>Gasket material:</b>		PUR			
Temperatures:					
<b>Short term:</b>		-40 ... 120 °C			
<b>Continuous:</b>		-40 ... 80 °C			
<b>Short term:</b>		-40 ... 250 °F			
<b>Continuous:</b>		-40 ... 175 °F			
Accessories:					
MPS ARCA 3020		Mounting plate			
MPP ARCA 3020		Mounting plate perforated			
MPX ARCA 3020		Mounting plate			
DRS ARCA 302015		DIN rail frame set			
DRS ARCA 302021		DIN rail frame set			
IDS ARCA 3020		Inner door set			
PMK ARCA 20		Pole mounting kit			
		Electrical insulation: Totally insulated			
		Halogen free (DIN/VDE 0472, Part 815): Yes			
		UV resistance: UL 508			
		Glow Wire Test (IEC 695-2-1) °C: 960			
Certificates:		Fimko			

ARCA 300x200x150

ARCA 200x300x150

