



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	OWN	APVD
H	—		G4	REV PER ECR-10-000662	18JAN2010	JY	SY
			H	ECR-10-018652	10SEP10	SW	MQW

D



C

B


A



SECTION A-A



COMPONENT SIDE AS SHOWN
RECOMMENDED PCB-HOLE LAY-OUT
SCALE 2,5:1



P.C.B. HOLE DIM. ACTION PIN
FOR DETAILS SEE
APPLICATION SPECIFICATION

NOTES:

1. MATERIAL CONTACTS; PHOSPHORBRONZE
MATERIAL SHIELD ; PHOSPHORBRONZE
MATERIAL HOUSING; GLASSFILLED POLYESTER (GRAY)
2. GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1,27µm NICKEL MIN.AND ACTION
PIN: 0,5µm TIN-LEAD MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
3. CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 2.
4. CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 1.
5. CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE
QUALITY LEVEL III,CENTRAL OFFICE APPLICATIONS.
6. CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE
APPROVED LUBRICANT.
7. PLATING SHIELD
CONTACT AREA : 0,76µm Au MIN.
ACTION PIN : 0,5µm SnPb MIN.
REMAINDER : Ni
8. ASSEMBLY PRINTED WITH P/N AND DATECODE
THE MARKING CAN APPEAR ON THE FRONT SIDE
OR BACK SIDE.
9. HOLE PATTERN FOR FEMALE CONNECTOR TYPE C
55 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
10. ROW "f" 6 PLATED THROUGH HOLES FOR UPPERSHIELD
11. SHIELD MOUNTED ON CONNECTOR WITH DOUBLE SIDED
ADHESIVE TAPE OR ADHESIVE
12. FITS WITH LOWERSHIELD, BASIC PARTNUMBER : 352112.
13. 0.76µm MIN GOLD PLATING AT MATING SURFACES.

2 3 7 1 3	1	3-352115-0
2 5 6 7	1	352115-9
2 4 7	1	352115-4
2 3 7	1	352115-1
FINISH	MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. TRUREN	20JAN97	Tyco Electronics Tyco Electronics Corporation s-HertogenBosch,Netherlands,		
DIMENSIONS: MM		CHK —	—			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2		APVD —	—	NAME Z-PACK 2mm HM TYPE C - 11 COLUMNS PRE-SHIELDED RECEPTACLE		
MATERIAL —		PRODUCT SPEC 108-19082	—	SIZE A2	CAGE CODE 00779	DRAWING NO C-352115
FINISH —		APPLICATION SPEC 114-19029	—	WEIGHT —	RESTRICTED TO —	—
CUSTOMER DRAWING				SCALE NTS	SHEET 1 OF 1	REV H