

Datasheet

RS Pro Miniature Power Tool Variable Speed Transformer, 230; 3 to 12V, Euro & UK Plug

RS Stock No: 472-3123



Product Details

RS Pro variable speed transformer miniature power tool has a voltage rating of 230 and 3 to 12 V. It has type C - Euro and plug and type G - British 3-pin. The microchip electronic variable speed control is suitable for smooth running of tools.

Features and Benefits

- 3 outputs for ease of tool changeover
- Microchip electronic variable speed control for smooth running of tools
- Full torque for effective use of tools at slow speeds
- Resettable overload cut-off provides protection
- Top of unit has storage facility for up to 60 accessories and tool rest for quick an easy access
- Input voltage 230-240 V ac
- Output voltage 3 to 12 V dc



ENGLISH

Specifications:

Plug Type	Type C - Euro Plug, Type G - British 3-Pin
Power Output	100 W
Type	Variable Speed Transformer
Voltage Rating	230; 3 to 12 V