





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
H	—		D1	ECR-06-002635	07-02-06	BSV	BM
			D2	REVISED PER ECO-09-021510	11SEP09	KK	AEG
			E	ECR-10-019054	15SEP10	DP	MQW

ALTERNATE FORM

- NOTES:
- MATERIAL CONTACT: PHOSPHORBRONZE
MATERIAL HOUSING: GLASSFILLED POLYESTER
UL-RATING 94V0 (GRAY)
 - GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27µm NICKEL MIN.AND ACTION PIN: 0,5µm TIN-LEAD MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
 - CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.
 - CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 1.
 - CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
 - CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III, UNCONTROLLED ENVIRONMENT APPLICATIONS.
 - CONNECTOR LUBRICATED WITH TELCORDIA APPROVED LUBRICANT.
 - CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE.
 - PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID (95 HOLES).
 - HOLES IN ROW f AND z FOR POSSIBLE FUTURE USE OF GROUND RETURN SHIELD. (SHIELDS NOT YET TOOLED)
 - OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



1 OBSOLETE	2 6 7	1	1-352269-9								
	2 5 7	1	352269-9								
	2 4	1	352269-4								
	2 3	1	352269-1								
	FINISH		MATERIAL	PARTNUMBER							
OCUMENT.	DWN L.V.D.HEIJDEN 30JUL97	Tyco Electronics Tyco Electronics Corporation s-HertogenBosch,Netherlands,									
	CHK D.TRUREN 30JUL97										
S UNLESS SPECIFIED:	APVD F.V.KONINGSBRUGGE -	NAME									
	PRODUCT SPEC	Z-PACK 2MM HM TYPE B									
	±0.2	95 POS. 19 COLUMNS VERTICAL FEMALE									
	APPLICATION SPEC	CONNECTOR ASSEMBLY									
	114-19029	SIZE	CAGE CODE	DRAWING NO							
WEIGHT	-	A2	00779	C-352269	RESTRICTED TO	-					
CUSTOMER DRAWING				SCALE	NTS	SHEET	1	OF	1	REV	E