

# Power Commander PDU/120V /30A/single phase/24 pcs 5-20R O/L

3A44B2-1



Two 15A resettable circuit breakers.  
Twenty-four 20A outlets with T-slots, gray  
housing. 12' [3.6m] cord. Length 48" [1.3m].

## features & benefits



## specifications

### Technical Information

Amps: 30  
Mounting: 0U  
Rated Voltage: 120V  
Number Of Circuits: 2  
Receptacle Type: NEMA  
Network Monitoring: No  
Number Of Outlets: 24

### Buy American Act Compliance

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant