

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

.19

© COPYRIGHT 19

BY AMP INCORPORATED.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1 OF 2

508

+1
-2.5

SECT "A" - "A"

SECT "B" - "B"

SEE
DETAIL "A"

P13S,M

P/N 5-912057-3

REC ASS'Y (H=6mm), 0.8mm BTB

STACKING CONN.

Tyco Electronics

0.6 ± 0.3

(8.5)

+0.4
-0.1

12.5

(15.2)

±0.3
2.1

±0.3
0.6

±0.3
7.3


±0.3
0.6

DETAIL "A"
(SCALE 5-1)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.20
2 PLC ±0.25
3 PLC ±0.30
4 PLC ±
ANGLES ±3°

MATERIAL



FINISH



DWN

FLORENCE TAN

CHK

ERIC TNG

APVD

SEI FONG

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

16AUG04

Tyco Electronics
(Singapore) Pte. Ltd.

NAME
RECEPTACLE ASSEMBLY 13H TYPE
FOR FH 0.8mm PITCH B-T-B CONNECTOR

SIZE

A3

CAGE CODE

00779

DRAWING NO

5179010

SCALE 4:1

SHEET 2 OF 2

REV 02

	84.20	85.80	79.20	200	6-	-0
	76.20	77.80	71.20	180	5-	-9
	68.20	69.80	63.20	160	5-	-8
	60.20	61.80	55.20	140	5-	-6
	52.20	53.80	47.20	120	5-	-5
	44.20	45.80	39.20	100	5-	-4
	36.20	37.80	31.20	80	5-	-3
	28.20	29.80	23.20	60	5-	-2
0.5	20.20	21.80	15.20	40	5-	-1
	84.20	85.80	79.20	200	1-	-0
	76.20	77.80	71.20	180		-9
	68.20	69.80	63.20	160		-8
	60.20	61.80	55.20	140		-6
	52.20	53.80	47.20	120		-5
	44.20	45.80	39.20	100		-4
	36.20	37.80	31.20	80		-3
	28.20	29.80	23.20	60		-2
0.8	20.20	21.80	15.20	40		-1
D	C	B	A	POS.	PART No.	