

Datasheet

Art.No. 92.050.0353.1

Distributor GST18i5V 3P1 V SW

Distribution block GST18i5, 5 pole, 1 input and 3 outputs 5 pole, 250/400 V, 20 A, colour of coding: black



Art.No.	92.050.0353.1
EAN	4015573381681
Order unit	60 pieces

Approvals



Technical data

General

Rated current	20 A
Rated voltage	400 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	

Model

Number of poles	5
Number of poles 2	3
Number of inputs	1
Number of outputs	3
Type of fastening	No
Degree of protection (IP)	IP40
Type of distributor	Distribution terminal block

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn

Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	44 mm
Width	55 mm
Height	39 mm

Drawings

A

B

C

D

E

Diese Maße werden bei: Anatomic besonders geprüft
Ausschließlich Prüfmaße
MIT JE gekennzeichnete Maße sind nur für interne Zwecke gültig

Weitere Daten siehe Katalog
further data see catalog

Teile - Nr. part-no.	Farbe colour	Typ type
92.050.0353.0	weiß white	GST1815V 3P1 V WS
92.050.0353.1	schwarz black	GST1815V 3P1 V SW

Freitoleranz nach DIN -

CAD - Zeichnung, keine manuellen Änderungen

1.Verwendung: -

Bl.: 1 von 1

	/	Maßstab	2004	Tag	Name	T	Zeichnung Nr. 92.050.0353.0 01K	Index Page: 4 of 4
	/	%	Entworfen	08.12.	Treschan			
	/		Geprüft	-	-			

DWG028 treeplan 2004-12-10T10:20:58 1000