







RECOMMENDED HOLE LAYOUT FOR
.070/(1.78) MAX. THICK P. C. BOARD



NOTES:

- 1) HOUSING MATERIAL:
NYLON 6/6, U.L. 94V-2, COLOR: NATURAL.
NYLON 6/6, U.L. 94V-0, COLOR: NATURAL.
- 2) TERMINAL MATERIAL: COPPER ALLOY
- 3) TERMINAL PLATING:
 - 1 - .000100/(.00254) MIN. BRIGHT TIN OVER .000050/(.00127) MIN. NICKEL OVERALL
 - 2 - .000030/(.00080) MIN. SELECT GOLD, .000100/(.00254) MIN. MATTE TIN OVER .000050/(.00127) MIN. NICKEL OVERALL
- 4) PART IS DESIGNED IN METRIC.
- 5) PART MATES WITH MINI-FIT JR. RECEPTACLE NO. 5557.
- 6) PRODUCT SPECIFICATION: PS-45750-001
- 7) PART ARE NOT TO BE MATED OR UN-MATED WHILE CIRCUITS ARE LIVE.
- 8) PARTS TO HAVE "HCS+" MARKING
- 9) PACKAGING SPECIFICATION: PK-5566-001.
- 10) PART CONFORMS TO CLASS B OF COSMETIC SPECIFICATION PS-45499-002.



NOTE 9: CHG PKG. SPEC. EC NO: UCP2009-0751 DWG:BM RKUS 2008/09/29 CHK:DBM RKUS 2008/09/29 APPR:BM RKUS 2008/10/02	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		▽=0 ◻=0	mm	INCH	DRAWN BY TGREGORI	DATE 2006/04/27	TITLE VERTICAL HEADER ASSEMBLY DUAL ROW MINI-FIT PLUS HCS SERIES MOLEX INCORPORATED	DOCUMENT NO. SD-46015-001	SHEET NO. 1 OF 2	
		4 PLACES ± --- ± ---	3 PLACES ± --- ± .010	CHECKED BY JCOMERC	DATE					
		2 PLACES ± 0.25 ± .015	1 PLACE ± 0.38 ± ---	APPROVED BY JCOMERC	DATE					
		ANGULAR ±1/2°		MATERIAL NO.						
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

[illegible]