




THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - By -

LOC	DIST	REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	DWN
		A1		REVISED PER ECO-11-004835	11MAR11	RK



1. ALL PARTS PACKAGED UNASSEMBLED.
2. THIS KIT CONSISTS OF 2 STRAIN RELIEF HALVES, 2 #4-40 SCREWS, 2 #4-40 NUTS & 2 #4-40 MOUNTING SCREWS.
- 3

 ZINC PLATED .000200-.000400 THICK, CLEAR CHROMATE COATING.

OBSOLETE	D	.280	5745833-9
	G	.350	5745833-7
	K	.430	5745833-5
	M	.480	5745833-3
	P	.530	5745833-1
	SIZE IDENT LETTER	CABLE DIA	PART NO.

COPYRIGHT 2005
TE CONNECTIVITY CORP
ALL RIGHTS RESERVED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. HENNY 8-13-05	TE Connectivity			
DIMENSIONS: INCHES		CHK C. ROHDE 8-13-05				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CABLE CLAMP KIT, SIZE 3, 25 POSN, 180 DEG,			
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		AMPLIMITE SERIES, PLATED PLASTIC			
MATERIAL SEE CALLOUTS		FINISH SEE CALLOUTS	APVD M. WALMSLEY 8-13-05	PRODUCT SPEC	SIZE A2	CAGE CODE 00779
			APPLICATION SPEC	WEIGHT -	DRAWING NO C=5745833	RESTRICTED TO -
			CUSTOMER DRAWING	SCALE 1:1	SHEET 1 of 1	REV A1