

KEMET Part Number: C1210X105K5RACTU
(C1210X105K5RAC7800)

Capacitor, Ceramic, SMD, MLCC, FT-CAP, Temp Stable, 1 uF, +/-10% Tol, 50 V, X7R, 1210 (3225 metric)



| General Information | |
|--------------------------|--------------------------------|
| Supplier: | KEMET |
| Application: | Standard Chip |
| Chip Size: | 1210 (3225 metric) |
| Temperature Coefficient: | X7R |
| Part Type Description: | SMD, MLCC, FT-CAP, Temp Stable |
| Termination Type: | Flexible Termination |
| Marked: | No |
| RoHS: | Yes |

| Dimensions (mm) | | |
|-----------------|-----------|-----------|
| Symbol | Dimension | Tolerance |
| L | 3.3 | +/-0.4 |
| W | 2.6 | +/-0.3 |
| T | 1.55 | +/-0.20 |
| B | 0.6 | +/-0.25 |

| Packaging Specifications | |
|--------------------------|--------------|
| Package Kind: | T&R |
| Package Size: | 7 in/180 mm |
| Package Type: | Plastic Tape |
| Package Quantity: | 2000 |

| Specifications | |
|------------------------|--|
| Capacitance: | 1 uF |
| Voltage: | 50 V |
| Tolerance: | +/-10% |
| Temperature Range: | -55/+125C |
| Dissipation Factor: | 2.5% |
| Failure Rate: | N/A |
| Aging Rate: | 3% loss/decade hour |
| Insulation Resistance: | 500 MOhm |
| Dielectric Strength: | 125 V |
| Miscellaneous: | Note: Referee time for X7R dielectric for this part number is 1000 hours |