



Lithium-ion cordless screwdriver
IXO



IXO



- Automatic spindle lock for manual tightening or loosening of screws
- Optimum storage in the charging station
- Softgrip for a better and more comfortable hold

Part no. 0 603 959 370

- Charger
- Bit set holder with 10 bits incl. Ikea bit

Technical data

Screw diameter up to	5 mm
No-load speed	180 rpm
Max. torque	3 Nm
Battery voltage	3,6 V
Charging time	5 h
Chucks	Magnetic bit holder with hexagonal shank
Machine weight	0,30 kg

Functions

- Forward/reverse operation
- Forward/reverse indicator
- Integrated work light
- Charge level indicator
- Softgrip

Noise/vibration information

Show values

Measured values determined according to EN 60745

Total vibration values (vector sum of three directions)

Screwdriving

Vibration emission value ah 2,5 m/s²

Uncertainty K 1,5 m/s²

The A-rated noise level of the power tool is typically as follows: Sound pressure level 70 dB(A); Sound power level 80 dB(A). Uncertainty K= 3 dB.

