

# HIGH PROTECTION RIGID CASES

## COMPOSITIONS (1/2)

### » 4750RCHDW01FF3

194 PCS

For general purpose.  
Metric 1/4", 3/8".



#### FF2B12 - 92 pcs

**6700SM** SOCKET 1/4", AEROSPACE, SHORT SERIES

5.5, 6, 7, 8, 9, 10, 11, 12, 13

**A6800DM** SOCKET 1/4", AEROSPACE LONG SERIES

5.5, 6, 7, 8, 9, 10, 11, 12, 13

**6709M** SOCKET DRIVER 1/4", HEX 3, 4, 5, 6, 8

**6709PH** SOCKET DRIVER 1/4", PH 1, 2, 3

**6709TORX** SOCKET DRIVER 1/4", TORX®

T8, T9, T10, T15, T20, T25, T27, T30, T40

**6950SL** REVERSIBLE RATCHET 1/4", SLIMHEAD

**6954** T-HANDLE 1/4"

**6956** SPINNER HANDLE 1/4"

**6958** BREAKER BAR 1/4"

**6960 / 6962** EXTENSION BARS 1/4" 50, 100, 150 mm

**6962L** EXTENSION BAR 1/4" 355 mm

**6966** UNIVERSAL JOINT 1/4"

**6972H** BIT HOLDER 1/4"

**7764** ADAPTOR F 3/8" - M 1/4"

**7400SM** SOCKET 3/8" SHORT SERIES 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 22

**A7402DM** SOCKET 3/8", AEROSPACE 10, 11, 12, 13, 14, 15, 16, 17, 18, 19

**7409M** SOCKET DRIVER 3/8" HEX 3, 4, 5, 6, 7, 8, 10

**7409TORX** SOCKET DRIVER 3/8", TORX® T25, T27, T30, T40, T45, T50

**7750SL** RATCHET 3/8" SLIMHEAD

**7760 / 7762** EXTENSION BARS 3/8" 75, 125, 250 mm

**7766** UNIVERSAL JOINT 3/8"

**7765** ADAPTOR F 1/4" - M 3/8"

**8164-1/2** ADAPTOR F 3/8" - M 1/2"

**7407H** SOCKET HOLDER 3/8" 1/4" - 3/8"



#### FF2B13 - 39 pcs

**111M** COMBINATION WRENCH 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21, 22

**6M** OPEN END WRENCH 6x7, 8x9, 10x11, 12x13, 14x15, 16x17, 18x19, 20x22

**BE-9770** BLACK HEX KEYS SET, LONG BALL END, 9 PCS 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10 mm

**9070C** ADJUSTABLE WRENCH CHROMED 6" ERGO™ 158x20 mm

**1177-SCRIBE** OFFSET SCRIBER 230 mm

**2535F2** MAGNETIC PICK UP 1 kg

**7758** BREAKER BAR

**BFLA01** Q3 LED-TORCH

**7754** T-HANDLE 3/8"

# HIGH PROTECTION RIGID CASES COMPOSITIONS (2/2)

## » 4750RCHDW01FF3 194 PCS

For general purpose.  
Metric 1/4", 3/8".



### FF2B14 - 48 pcs

**808050P** PISTOL HANDLE  
RATCHETING SCREWDRIVER

**808050S** RATCHETING  
SCREWDRIVER, STUBBY

**59S/31-1** BITS SET  
31 PCS: PH, PZ, TORX®, HEX, SL

**2047-0.8-4** OFFSET SCREWDRIVER  
0,8X4X100

**2047PR-1-2** DOUBLE OFFSET KEY  
FOR PHILLIPS SCREWS  
PH1 & 2

**BE-8020L** SCREWDRIVER ERGO™,  
SLOTTED  
0,5X3X75

**BE-8030** SCREWDRIVER ERGO™,  
SLOTTED  
0,6X3,5X75

**BE-8155** SCREWDRIVER ERGO™,  
SLOTTED  
1,2X6,5X125

**BE-8260** SCREWDRIVER ERGO™,  
SLOTTED, HEX PROFILE & BOLSTER  
1,6X8,0X175

**BE-8350** SCREWDRIVER ERGO™  
SLOTTED, STUBBY  
1X5,5X25

**BE-8601 / BE-8602** SCREWDRIVERS  
ERGO™, PHILLIPS, STUBBY  
PH1X25, PH2X25

**BE-8610 / BE-8630** SCREWDRIVERS  
ERGO™, PHILLIPS  
PH1X75, PH2X100, PH3X150

**2058-BR** BIT-RATCHET 1/4"

**1544** FEELER GAUGE

**2509** FLEXIBLE PICK-UP TOOL  
525 mm



### FF2B15 - 9 pcs

**MTB-3-16-E** MEASURING TAPE  
ENGLISH  
3 m

**2101GC-160IP** SIDE CUTTING PLIER,  
ERGO™  
160 mm

**2427 GC-200IP** LONG, ROUND NOSE  
CHROMED PLIER, ERGO™  
200 mm

**2430 GC-200 IP** SNIPE NOSE  
CHROMED PLIER, ERGO™  
200 mm

**2628 GC-160IP** COMBINATION  
CHROMED PLIER, ERGO™  
160 mm

**8224CIP** SLIP JOINT PLIER, ERGO™

**1150-1/2H/P** CALIPER  
150 mm

**5515T-52** TELESCOPIC SWIVEL  
HEAD MIRROR  
Ø 50 mm

**2820EF2** ELECTRICIANS KNIFE



### FF2B16 - 6 pcs

**481-300** DIN HAMMER  
300 mm

**3625W-35** NYLON TIP HAMMER

**3734** DRIFT PUNCHES  
Ø 3, 5, 8 mm

**3735-4-120** CENTRE PUNCH  
120 mm