


# Housing - UM100-PROFIL 200CM - 2906319

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Profile housing and board base, with a constructional width of 100 mm and a fixed length of 200 cm



## Key commercial data

Packing unit	1 CM
GTIN	 4 017918 277451
Weight per Piece (excluding packing)	955.0 g
Custom tariff number	39162000
Country of origin	Germany

## Technical data

### General

Housing type	Panel mounting base
Housing material	PVC
Color	green

### Ambient conditions

Ambient temperature (operation)	-15 °C ... 50 °C
---------------------------------	------------------

### Dimensions

Length	2 m
Width	2000 mm

### Technical data

Inflammability class according to UL 94	V0
---	----

## Classifications

### eCl@ss

eCl@ss 4.0	27180401
------------	----------

# Housing - UM100-PROFIL 200CM - 2906319

## Classifications

### eCl@ss

eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701

### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC000721

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## Accessories

### Accessories

#### Component housing cover

Electronic housing - UM-A/U N 73 CM - 2706852

U-shaped cover, flat-profile version, transparent, PC, high-temperature resistant material, please indicate length in [cm] with order no.

---

#### Component housing lower part

Electronic housing - UM108-LG 10 - 2959780

Profile housing and board base, 10 mm wide module, consisting of two side elements



---

#### Mounting material

## Housing - UM100-PROFIL 200CM - 2906319

### Accessories

Electronic housing - UM108-FE - 2959463

Foot element, 107.5 mm wide, for mounting on NS 32 or NS 35/7.5, below profile housing UM 108.



Mounting flange - UMK-BF - 2976077



Mounting flange, for mounting directly on the wall

Electronic housing - UM108-FE - 2959463

Foot element, 107.5 mm wide, for mounting on NS 32 or NS 35/7.5, below profile housing UM 108.



Mounting flange - UMK-BF - 2976077



Mounting flange, for mounting directly on the wall

Panel mounting base side part

Electronic housing - UM108-SE - 2959476

Side element, 5 mm wide, PCB width: 107.5 mm



## Housing - UM100-PROFIL 200CM - 2906319

### Accessories

Electronic housing - UM108-SEFE/R-A60 - 2959706



Side element, with foot, tall version, right-hand, for 60 mm wide U-shaped cover.

---

Electronic housing - UM108-SEFE/R-A73 - 2959719



Side element, with foot, tall version, right-hand, for 73 mm wide U-shaped cover.

---

Electronic housing - UM108 N-SEFE/R-A73 - 2709354



Side element, with foot, low-profile version, right-hand, for 73 mm wide U-shaped cover.

---

Electronic housing - UM108-SEFE/L-A60 - 2959722



Side element, with foot, tall version, left-hand, for 60 mm wide U-shaped cover.

---

Electronic housing - UM108-SEPEF/L-A60 - 2906500



Side element with foot, tall design, left-hand, for 60 mm wide U-shaped cover, with PE contact to the DIN rail.

---

## Housing - UM100-PROFIL 200CM - 2906319

### Accessories

Electronic housing - UM108-SEFE/L-A73 - 2959735



Side element, with foot, tall version, left-hand, for 73 mm wide U-shaped cover.

---

Electronic housing - UM108-SEPEF/L-A73 - 2906513



Side element with foot, tall design, left, for 73 mm wide U-shaped cover, with PE contact to the DIN rail.

---

Electronic housing - UM108 N-SEFE/L-A73 - 2709367



Side element, with foot, low-profile version, left-hand, for 73 mm wide U-shaped cover.

---

Electronic housing - UM108 N-SEPEF/L-A73 - 2709370



Side element with foot, low-profile design, left, for 73 mm wide U-shaped cover, with PE contact to the DIN rail.

---

Electronic housing - UM108-SE-A60 - 2959748



Side element, without foot, tall version, for 60 mm wide U-shaped cover.

---

# Housing - UM100-PROFIL 200CM - 2906319

## Accessories

Side element - UM108-SE-A73 - 2959751



Side element, without foot, tall version, for 73 mm wide U-shaped cover.

Electronic housing - UM108 N-SE-A73 - 2709383



Side element, without foot, low-profile version, for 73 mm wide U-shaped cover.

Electronic housing - UM108-A/U CM - 2854898

Profile covers, tall version, widths of 60 mm (internal dimension 56 mm) and 73 mm (internal dimension 69 mm) are available. Please note the ordering example and the order key.

## Drawings

Dimensioned drawing

