

Thrust ball bearings, single direction



Principal dimensions			Basic load ratings		Fatigue load limit	Minimum load factor	Speed ratings		Mass	Designation
d	D	H	dynamic	static	P_u	A	Reference speed	Limiting speed		
mm			kN	C ₀	kN	-	r/min		kg	-
15	28	9	10,6	18,3	0,67	0,0017	8500	12000	0,024	51102

