

SOLID PC 3819 13 G-2FSH



Sample photo

Order symbol: PC 3819 13 G-2FSH
Product nbr: 2539513
Description: Enclosure, PC
Remarks: Grey hinged cover

EAN: 6418074052735
EI. number:
Finland: 3435726
Electric No. Sweden: 2539513

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	378	188	130	EKMXT	Mounting plate Pertinax
inch:	14.9	7.4	5.1	EKV 12	DIN-35 Mounting rail
				EKV 32	DIN-35 Mounting rail
				EKMZR	Extension frame
Materials:				Rating:	
Material:	Polycarbonate			Ingress Protection (EN 60529): IP65	
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK08/IK09	
Cover screws material:	Polyamide			Electrical insulation: Totally insulated	
Cover colour:	RAL 7035 -light grey			Halogen free (DIN/VDE 0472, Part 815): 1	
Cover screws colour:	Grey			UV resistance: UL 508	
Gasket material:	Polyurethane			Flammability Rating: UL 746C 5V	
				Glow Wire Test (IEC 695-2-1) °C: 960	
Temperatures:				Certificates:	
Temperature °C (short term):	-40 ... 120 °C			SGS Fimko	
Temperature °C (continuous):	-40 ... 80 °C			Gost R	
Temperature °F (short term):	-40 ... 250 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
EKMVT	Mounting plate				

