

SOLID PC 3828 18 G



Sample photo

Order symbol: PC 3828 18 G
Product nbr: 5330373
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074005588
El. number:
Finland: 3423719
Italy: 7401055
Sweden: 2539424

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:	
mm:		378	278	180	Ingress Protection (EN 60529): IP 66/67	
inch:		14.9	10.9	7.1	Impact Resistance (EN 62262): IK 08/09	
Materials:					Electrical insulation: Totally insulated	
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes	
Base colour:		RAL 7035			UV resistance: UL 508	
Cover colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 5V	
Cover screws material:		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960	
Cover screws colour:		Grey			NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12	
Gasket material:		Polyurethane			Certificates:	
Temperatures:						
Short term:		-40 ... 120 °C				Underwriters Laboratories
Continuous:		-40 ... 80 °C				Fimko
Short term:		-40 ... 250 °F				Europe EN 62208: 2003
Continuous:		-40 ... 175 °F				
Accessories:						
EKPVT		Mounting plate				
EKV 22		DIN-35 Mounting rail				
EKV 32		DIN-35 Mounting rail				
EKPZR		Extension frame				

