



## **SANDFLEX® Bi-metal blades**

**3840 ST**

- The Sandflex® standard shaped with improved performance and precision-ground teeth
  - Virtually unbreakable Sandflex® bi-metal blade for all materials and type of cut
  - Specially developed for cutting metal
  - Standard (ST) shape for fast and aggressive straight cuts
  - Available in two different packaging alternatives:
    1. An innovative self-service pack, -5P = 5 blades per cassette
    2. Industrial pack, -10P = 10 blades per box
- Most popular items also available bulk packed, -100P = 100 blades per box





# RECIPROCATING SAWBLADES



Bahco

| <b>3840-100-6-ST-5P</b>      | 7311518235642 | 5 | 100 | 1,27 | 6    | ST | 95   |
|------------------------------|---------------|---|-----|------|------|----|------|
| <b>3840-100-10-ST-5P</b>     | 7311518235840 | 5 | 100 | 0,89 | 10   | ST | 58   |
| <b>3840-100-14-ST-5P</b>     | 7311518235932 | 5 | 100 | 0,89 | 14   | ST | 75   |
| <b>3840-100-18-ST-5P</b>     | 7311518236052 | 5 | 100 | 0,89 | 18   | ST | 75   |
| <b>3840-100-24-ST-5P</b>     | 7311518236168 | 5 | 100 | 0,89 | 24   | ST | 75   |
| <b>3840-150-6-ST-5P</b>      | 7311518235680 | 5 | 150 | 1,27 | 6    | ST | 145  |
| <b>3840-150-8/12-ST-5P</b>   | 7311518235758 | 5 | 150 | 0,89 | 8/12 | ST | 120  |
| <b>3840-150-10-ST-5P</b>     | 7311518235871 | 5 | 150 | 0,89 | 10   | ST | 120  |
| <b>3840-150-14-ST-5P</b>     | 7311518235956 | 5 | 150 | 0,89 | 14   | ST | 120  |
| <b>3840-150-18-ST-5P</b>     | 7311518236076 | 5 | 150 | 0,89 | 18   | ST | 120  |
| <b>3840-150-24-ST-5P</b>     | 7311518236182 | 5 | 150 | 0,89 | 24   | ST | 120  |
| <b>3840-228-8/12-ST-5P</b>   | 7311518235789 | 5 | 228 | 1,27 | 8/12 | ST | 170  |
| <b>3840-228-10-ST-5P</b>     | 7311518235901 | 5 | 228 | 0,89 | 10   | ST | 170  |
| <b>3840-228-14-ST-5P</b>     | 7311518235987 | 5 | 228 | 0,89 | 14   | ST | 170  |
| <b>3840-228-18-ST-5P</b>     | 7311518236106 | 5 | 228 | 0,89 | 18   | ST | 175  |
| <b>3840-300-14-ST-5P</b>     | 7311518236014 | 5 | 300 | 0,89 | 14   | ST | 230  |
| <b>3840-300-18-ST-5P</b>     | 7311518236137 | 5 | 300 | 0,89 | 18   | ST | 230  |
| <b>3840-100-14-ST-10P</b>    | 7311518238650 | 1 | 100 | 0,89 | 14   | ST | 115  |
| <b>3840-100-18-ST-10P</b>    | 7311518238667 | 1 | 100 | 0,89 | 18   | ST | 115  |
| <b>3840-100-24-ST-10P</b>    | 7311518238674 | 1 | 100 | 0,89 | 24   | ST | 115  |
| <b>3840-150-6-ST-10P</b>     | 7311518238766 | 1 | 150 | 1,27 | 6    | ST | 250  |
| <b>3840-150-8/12-ST-10P</b>  | 7311518238773 | 1 | 150 | 0,89 | 8/12 | ST | 170  |
| <b>3840-150-10-ST-10P</b>    | 7311518238698 | 1 | 150 | 0,89 | 10   | ST | 185  |
| <b>3840-150-14-ST-10P</b>    | 7311518238704 | 1 | 150 | 0,89 | 14   | ST | 185  |
| <b>3840-150-18-ST-10P</b>    | 7311518238711 | 1 | 150 | 0,89 | 18   | ST | 170  |
| <b>3840-150-24-ST-10P</b>    | 7311518238728 | 1 | 150 | 0,89 | 24   | ST | 185  |
| <b>3840-228-8/12-ST-10P</b>  | 7311518238834 | 1 | 228 | 1,27 | 8/12 | ST | 290  |
| <b>3840-228-10-ST-10P</b>    | 7311518238780 | 1 | 228 | 0,89 | 10   | ST | 290  |
| <b>3840-228-14-ST-10P</b>    | 7311518238797 | 1 | 228 | 0,89 | 14   | ST | 290  |
| <b>3840-228-18-ST-10P</b>    | 7311518238803 | 1 | 228 | 0,89 | 18   | ST | 295  |
| <b>3840-300-14-ST-10P</b>    | 7311518238841 | 1 | 300 | 0,89 | 14   | ST | 395  |
| <b>3840-300-18-ST-10P</b>    | 7311518238858 | 1 | 300 | 0,89 | 18   | ST | 390  |
| <b>3840-150-8/12-ST-100P</b> | 7311518235772 | 1 | 150 | 0,89 | 8/12 | ST | 1700 |
| <b>3840-150-10-ST-100P</b>   | 7311518235895 | 1 | 150 | 0,89 | 10   | ST | 1200 |
| <b>3840-150-14-ST-100P</b>   | 7311518235970 | 1 | 150 | 0,89 | 14   | ST | 1850 |
| <b>3840-150-18-ST-100P</b>   | 7311518236090 | 1 | 150 | 0,89 | 18   | ST | 1700 |
| <b>3840-150-24-ST-100P</b>   | 7311518236205 | 1 | 150 | 0,89 | 24   | ST | 1850 |
| <b>3840-228-8/12-ST-100P</b> | 7311518235802 | 1 | 228 | 1,27 | 8/12 | ST | 2800 |
| <b>3840-228-10-ST-100P</b>   | 7311518235925 | 1 | 228 | 0,89 | 10   | ST | 2800 |
| <b>3840-228-14-ST-100P</b>   | 7311518236007 | 1 | 228 | 0,89 | 14   | ST | 2800 |
| <b>3840-228-18-ST-100P</b>   | 7311518236120 | 1 | 228 | 0,89 | 18   | ST | 2950 |