



Datasheet

Stock No: 264-7364

ENGLISH

RS Pro M25 Nickel Plated Brass Cable Gland



Product Details:

IP68 Metric Gland

Glands for use with screened cable are designed to connect the screen of the cable to the enclosure screening system. This is achieved by the use of 2 tapered rings applying force onto an endless spring washer against the screen, to ensure a positive contact. Assembly is simple by exposing the screen, applying spring and washers then tightening the brass cable gland assembly. The gland bonds the screen to the housing.

Features and Benefits

- IP68 protection
- Quick and easy assembly
- Santoprene (polyolefin) rubber seal provides good weather and chemical resistance

Note: Not supplied with locknuts.

Standards: EN50262

Specifications:

Thread Size:	M25
Material:	Nickel Plated Brass
Maximum Cable Diameter:	11mm
Minimum Cable Diameter:	6mm
IP Rating:	IP68
Minimum Operating Temperature:	-40°C
Maximum Operating Temperature:	+135°C

