




ENGLISH


Datasheet

RS Pro Crimp Tool Open Barrel Terminal, 0.5 → 6.0 mm² Wire Size

RS Stock No.683-1611



Die profile



Crimp profile

CRB-0560 is a precision, ratchet crimp tool designed to provide consistent and reliable crimp connections on uninsulated open barrel connectors on wires ranging from 0,5-6,0 mm².

Easy to use

Open the tool. Insert terminal in correct nest. Close tool until terminal fastened. Insert wire into terminal. Close tool until ratchet release. Attention: To release ratchet mechanism, push the trigger.

Calibration

To calibrate this tool the pre-load has to be measured. Gauge is required to ensure that the die is according to specification. For more information See instruction sheet.

- Professional crimp tool for optimized crimp performance.
- Ergonomic handles for low effort crimping.
- Ratchet action to ensure full crimp cycle with safety release.
- Durable - minimum of 50,000 cycles.
- Tool is factory set with a precise eccentric cam adjustment function to guarantee performance.

Technical data

Lenght :	225 mm/8,86"
Height :	70 mm/2,76"
Weight :	540 gr/1,19 lbs
Connector:	Open barrel
Description:	Uninsulated
Wire size awg:	22-10 AWG
Wire size mm ² :	0,5-6,0 mm ² / 22-10 AWG