

9001KM35LG

Pushbutton+Pilot Light Light Module, Type: K, Size: 30mm

List Price \$77.00 USD

Availability **Non-Stock Item: This item is not normally stocked in our distribution facility.**

Technical Characteristics

Type	K
Approvals	UL File Number E42259 CCN NKCR - CSA File Number LR24590 Class 3211-03 - CE Marked
Light Module Supply Voltage	24/28V
Light Module Type	LED (Green)
Size	30mm
Terminal Type	Screw Clamp

Shipping and Ordering

Category	21435 - Modules, Light, Type KM
Discount Schedule	CP1
Article Number	785901028956
Package Quantity	1
Weight	0.14 lbs.
Availability Code	Non-Stock Item: This item is not normally stocked in our distribution facility.
Returnability	Y

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

For use in hazardous locations—See page 19-79.

- With neon type light modules, use a clear color cap only.
- With LED light modules, use either a clear color cap or a cap the same color as the LED.

New!

Table 19.219: Standard Light Modules for Types K, SK, and KX Control Units ♦



Voltage	Description	For Use With Single Lamp III. Operators as Indicated ▲	Light Module		Voltage Assembly Code	Rating	Replacement Lamp	
			Type	\$ Price			Part Number ♦	\$ Price
All	Full Voltage (without Bayonet Base Lamp)	All	KM40	52.	40	—	None	—
6 Vac/dc	Full Voltage	All	KM31	57.	31	.9 VA	2550101020	8.30
6 Vac/dc	LED Red	All Except ■	KM31LR	77.	31LR		6508805201	28.50
6 Vac/dc	LED Green	All Except ■	KM31LG	77.	31LG		6508805203	28.50
6 Vac/dc	LED Yellow	All Except ■	KM31LY	77.	31LY		6508805202	28.50
12–14 Vac/dc	Full Voltage	All	KM32	57.	32	1.2 VA	2550101037	8.30
12–14 Vac/dc	LED Red	All Except ■	KM32LR	77.	32LR		6508805201	28.50
12–14 Vac/dc	LED Green	All Except ■	KM32LG	77.	32LG		6508805203	28.50
12–14 Vac/dc	LED Yellow	All Except ■	KM32LY	77.	32LY		6508805202	28.50
18 Vac/dc	Resistor	All	KM33	57.	33	1.4 VA	2550101037	8.30
24–28 Vac/dc	Full Voltage	All	KM35	57.	35	1.2 VA	2550101002	8.30
24–28 Vac/dc	LED Red	All Except ■	KM35LR	77.	35LR	.28 VA	6508805210	28.50
24–28 Vac/dc	LED Green	All Except ■	KM35LG	77.	35LG	.28 VA	6508805212	28.50
24–28 Vac/dc	LED Yellow	All Except ■	KM35LY	77.	35LY	.28 VA	6508805211	28.50
24–28 Vac/dc	LED White	All Except ■	KM35LW	77.	35LW	.28 VA	6508805214	28.50
24–28 Vac/dc	LED Blue	All Except ■	KM35LL	77.	35LL	.28 VA	6508805213	28.50
48 Vac/dc	Full Voltage	All	KM36	57.	36	2.6 VA	2550101025	8.30
110–120 V, 50–60 Hz	LED Red	All Except ■	KM1LR	95.	1LR		6508805201	28.50
110–120 V, 50–60 Hz	LED Green	All Except ■	KM1LG	95.	1LG		6508805203	28.50
110–120 V, 50–60 Hz	LED Yellow	All Except ■	KM1LY	95.	1LY		6508805202	28.50
110–120 V, 50–60 Hz	Transformer	All Except ■	KM1	77.	1	2.4 VA	2550101020	8.30
110–120 V, 50–60 Hz	Flashing	All Except ■	KMF1	77.	F1	.85 VA	2550101036	11.00
120 Vac/dc	Resistor	All	KM38	57.	38	3.0 VA	2550101027	8.30
120 Vac/dc	Full Voltage	All	KM38	57.	38	3.0 VA	2550101027	8.30
120 Vac/dc	Neon	All Except ■	KM11	57.	11	0.2 VA	2550101013	21.90
120 Vac/dc	LED Red	All Except ■	KM38LR	77.	38LR	1.4 VA	6508805210	28.50
120 Vac/dc	LED Green	All Except ■	KM38LG	77.	38LG	1.4 VA	6508805212	28.50
120 Vac/dc	LED Yellow	All Except ■	KM38LY	77.	38LY	1.4 VA	6508805211	28.50
120 Vac/dc	LED White	All Except ■	KM38LW	77.	38LW	1.4 VA	6508805214	28.50
120 Vac/dc	LED Blue	All Except ■	KM38LL	77.	38LL	1.4 VA	6508805213	28.50
208–220 V, 50–60 Hz	Transformer	All Except ■	KM3	77.	3	2.5 VA	2550101020	8.30
208–220 V, 50–60 Hz	LED Red	All Except ■	KM3LR	95.	3LR		6508805201	28.50
208–220 V, 50–60 Hz	LED Green	All Except ■	KM3LG	95.	3LG		6508805203	28.50
208–220 V, 50–60 Hz	LED Yellow	All Except ■	KM3LY	95.	3LY		6508805202	28.50
220–240 V, 50–60 Hz	Transformer	All Except ■	KM7	77.	7	2.0 VA	2550101020	8.30
220–240 V, 50–60 Hz	LED Red	All Except ■	KM7LR	95.	7LR		6508805201	28.50
220–240 V, 50–60 Hz	LED Green	All Except ■	KM7LG	95.	7LG		6508805203	28.50
220–240 V, 50–60 Hz	LED Yellow	All Except ■	KM7LY	95.	7LY		6508805202	28.50
240 Vac/dc	Resistor	All Except ■	KM25	57.	25	6.0 VA	2550101027	8.30
240 Vac/dc	Neon	All Except ■ and KX	KM12	57.	12	0.3 VA	2550101013	21.90
277 V, 50–60 Hz	Transformer	All Except ■	KM8	77.	8	2.4 VA	2550101020	8.30
380–480 V, 50–60 Hz	Transformer	All Except ■	KM5	77.	5	2.8 VA	2550101020	8.30
480 Vac/dc	Neon	All Except ■ and KX	KM14	57.	14	0.5 VA	2550101013	21.90
550–600 V, 50–60 Hz	Transformer	All Except ■	KM6	77.	6	2.5 VA	2550101020	8.30

NOTE: Light modules are available in other voltages. For additional information, refer to Catalog 9001CT0001.

For use in hazardous locations—See page 19-79.

- Reduces the depth of illuminated push buttons with contact blocks by over 33%.
- With LED light modules, use either a clear color cap or a cap the same color as the LED.

Table 19.220: Shallow Depth Light Modules For Types K and SK Control Units ♦



Voltage	Description	Light Module		Voltage Assembly Code	Rating	Replacement Lamp	
		Type	\$ Price			Part Number	\$ Price
24–28 Vac/dc	Full Voltage	KM55	57.00	55	1.2 VA	2550101002	8.30
	LED Red	KM55LR	77.00	55LR	0.5 VA	6508805204	28.50
	LED Green	KM55LG		55LG		6508805206	
	LED Yellow	KM55LY		55LY		6508805205	
110–120 Vac/dc	Full Voltage	KM58	57.00	58	3.0 VA	2550101027	8.30
	LED Red	KM58LR	77.00	58LR	0.5 VA	6508805204	28.50
	LED Green	KM58LG		58LG		6508805206	
	LED Yellow	KM58LY		58LY		6508805205	

- ▲ 9001K, SK, KX.
- Do not use on any remote test version pilot light.
- ♦ For use with all operators except KX and remote test pilot.
- ★ Check light module label for series and replacement number.

When ordering, please specify:

- Quantity
- Class Number
- Type or Catalog Number



File CCN

E42259 NKCR



File Class LR25490 3211 03



marked