



Xitanium Outdoor SELV (Constant Current)

LED Driver Outdoor 17W/0.70A-24V 230V

Constant current LED driver for outdoor applications

Product data

• Product Data

Order code	913700615982
Full product name	LED Driver Outdoor 17W/ 0.70A-24V 230V
Order product name	LED Driver Outdoor 17W/ 0.70A-24V 230V
Pieces per pack	1
Packs per outerbox	10
Bar code on pack - EAN1	8711500930958
Bar code on outerbox - EAN3	8711500930965
Logistic code(s) - 12NC	913700615982
Net weight per piece	0.169 kg

• General Characteristics

Average Lifetime	50000 hr
Input Frequency	50 Hz
Type Version	mk2
IP Classification	IP66
Survival rate	90 %

• Operating Characteristics

Efficiency Range	80 %
Output Power Range	5.5-17.2 W
Power Factor (100% load)	0.9 -
Input Power max	6.8-21.5 W
Output Voltage Range	2.6-24.6 V

Output Current Range (mA)	665-735
Total Harmonic Distortion IEC	20 %
Type of Dimming	None

• Wiring Characteristics

Input Wire Length	150 mm
Input Wire Diameter	0.75 mm ²

• Temperature Characteristics

T-case maximum	90 C
T-ambient	-40 (min), 60 (max) C
T-Storage	-40 (min), 80 (max) C

• Approval&Application Char's

ENEC certificate	No
CE marking	Yes

• Product Dimensions

Length A1	132 mm
Width B1	34.2 mm
Height C1	25 mm
Fixing Hole Diameter D1	4.5 mm
Fixing Hole Distance Width B2	24.6 mm
Fixing Hole Distance Length A2	122.4 mm

PHILIPS

sense and simplicity