



NF
NORME FRANÇAISE



Approvals may be limited to certain products, see approvals on page 44.

PUSH-IN FITTING

Inserts into a 20mm knock-out, panel thickness up to 4mm, no locknut required. Black and grey.



SWIVEL COUPLER IP66

STRAIGHT PA66 BODY – SWIVEL COUPLER
For coupling to corrugated flexible conduit.
Black only.



3-WAY COUPLER IP66

3-WAY PA66 FITTING
For coupling to corrugated flexible conduit.
Black and grey.



REMOVAL TOOL

BLACK ONLY

Adaptalok removal tool, closes around the conduit, is then pushed into the fitting, releasing the retaining lugs allowing fitting to be removed.



NOMINAL CONDUIT SIZE mm	PART NUMBER	PART NUMBER	NOMINAL CONDUIT SIZE COMBINATION	PART NUMBER	PART NUMBER
13	-	AL13-AL13/A/000040	13x10x10	AL131010/Y	AL13RT
16	AL16/KM20/A	AL16-AL16/A/000040	16x13x13	AL161313/Y	AL16RT
21	AL21/KM20/A	AL21-AL21/A/000040	21x16x16	AL211616/Y	AL21RT
28	-	AL28-AL28/A/000040	28x21x21	AL282121/Y	AL28RT
34	-	AL34-AL34/A/000040	-	-	AL34RT
42	-	AL42-AL42/A/000040	-	-	AL42RT
54	-	-	-	-	AL54RT
13-34	-	-	-	-	ALRTSET

- See pages 38 - 45 for Technical Details
- See page 23 for Accessories
- See pages 34 - 35 for Cutting Tools and Instructions
- See page 36 for alternative female coupler

To order complete Part No, add colour - e.g. AL131010/Y/BL

Adaptalok fittings' simple push and twist mounting ensures high mechanical strength and IP66 assembly with Type PA/PR/PI/PP conduits, whilst unauthorised or accidental removal is prevented by the necessity to use a screwdriver or tool.

Lightweight aluminium or polyamide (Nylon) threaded swivel Adaptalok fittings (opposite page) provide simple coupling to UNEF threaded military style multi-pin connectors whilst Adaptalok couplers (this page) facilitate the connection of other conduits in various arrangements.

ADAPTALOK
SYSTEM
FROM ADAPTALEX



Compatible with fine and coarse pitch corrugated flexible conduit systems

Polyamide (Nylon) 66 body in black

Internal O-ring seal connector

Thread swivels for easy installation

www.adaptaflex.com