

2,8 mm	1,2...C manuell	0,3m	CS-Mount	94°17'	A0014
4,0 mm	1,2...C manuell	0,2m	CS-Mount	63°53'	A0021
4,8 mm Fixfocus	1,8...C manuell	0,2m	C-Mount	55°07'	A0016
6 mm	1,2...C manuell	0,2m	C-Mount	43°33'	A0053
8 mm	1,2...C manuell	0,3m	CS-Mount	33°19'	A0011
8,5 mm	1,5...C manuell	0,2m	C-Mount	31°52'	A0047
12 mm	1,2...22 manuell	0,2m	C-Mount	22°04'	A0035
16 mm	1,4...22 manuell	0,3m	C-Mount	16°55'	A0026
25 mm	1,4...22 manuell	0,3m	C-Mount	10°58'	A0007
35 mm	1,6...16 manuell	0,35m	C-Mount	7°51'	A0051
50 mm	2,8...22 manuell	0,9m	C-Mount	5°30'	A0052
50 mm	1,4...C manuell	1,0m	C-Mount	5°30'	A0049
75 mm	1,4...C manuell	1,2m	C-Mount	3°40'	A0008



A0016
4,8mm



A0011
8mm



A0026
16mm



A0007
25mm