

805-0976

151-00646

Cable Tie Mount-4 Way w/3M #5952 Adhesive 1.10" x 1.10" - BLK, T18-T50 Cable Ties, 500/pk

Article Number: 151-00646

Part Number: 151-00646

Type: MB4A



Base Data

Part No. 151-00646

Type MB4A

Color Black

Features HellermannTyton's 4-way mounting bases are available in four sizes to accommodate T18 through T150 series cable ties. Insertion of the ties can be made from all four sides. Each mount may be secured with two screws, with adhesive backing, or both, for ease of application and stability.

Application The UV stabilized mounts and VHB acrylic adhesive resists UV light and seals against moisture and environmental conditions, while providing strong bond to the surface.

Application Method These mounting bases can be secured to a surface using rubber based adhesive, acrylic adhesive, or also can be screw mounted.

Product Dimensions

Length (L) 1.10 " / 28.0 mm

Width (W) 1.10 " / 28.0 mm

Max. Cable Tie Width	0.21 " / 5.4 mm
-----------------------------	-----------------

Height (H)	0.19 " / 4.7 mm
-------------------	-----------------

Mounting Hole Ø	0.16 " / 4.0 mm
------------------------	-----------------

Mounting Hole Centers	0.80 " / 20.2 mm
------------------------------	------------------

Material and Specifications

Material	Polyamide 6.6 UV-stabilized (PA66UV)
-----------------	--------------------------------------

Flammability	UL94 V2 (excluding adhesive)
---------------------	------------------------------

Material Specification	RoHS
-------------------------------	------

Operating Temperature	-40 °C to +85 °C, intermittent +105 °C (for 500 h)
------------------------------	--