


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
		P	LTR	DATE	APVD
FT	0		L	REVISED PER 0G3B-0170-05	4/11/05 SS GS



- 1. NYLON, UL 94-VO RATED, RED.
- 2. PHOSPHOR BRONZE.
- 3. 3.81um [.000150] MIN TIN-LEAD OVER 1.27um [.000050] MIN NICKEL.
- 4. 0.76um [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81um [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.
- 5. .000150 MIN TIN OVER .000050 MIN NICKEL.
- 6. 0.76um [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81um [.000150] MIN TIN FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.

6	NO	1-207528-0
6	YES	207528-9
5	NO	207528-8
5	YES	207528-7
4	NO	207528-4
4	YES	207528-3
3	NO	207528-2
3	YES	207528-1
CONTACT FINISH		MOUNTING TABS
		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE 03/19/92	tyco Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
		CHK R.STONE 3-25-92		
		APVD A.TRAVIS 3-25-92	NAME SOCKET HEADER ASSEMBLY, 12 POSITION, METRIMATE	
		PRODUCT SPEC 108-10033		
		APPLICATION SPEC		
		WEIGHT -		
		CUSTOMER DRAWING		
		SCALE 4:1		
		SHEET 1 OF 1		
		REV L		