ENGLISH

Datasheet
HSS Jobber Drill Bit

Description:

Manufactured to DIN 338 with right hand spiral.

Point angle 118°.

Ideal for general workshop or maintenance use where precision and high productivity are not required.

Black finish for corrosion and wear protection.

Material: HSS M2

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

ENGLISH

RS Stock No.	Diameter(mm)	Overall Length (mm)	Flute Length (mm)
212-991	1.0	34	12
212-985	1.5	40	18
212-979	2.0	49	24
213-089	2.5	57	30
212-963	3.0	61	33
212-957	3.3	65	36
213-073	3.5	70	39
213-067	4.0	75	43
213-051	4.2	75	43
213-023	4.5	80	47
213-045	5.0	86	52
213-039	5.5	93	57
213-095	6.0	93	57
213-168	6.5	101	63
213-146	7.0	109	69
213-130	7.5	109	69
213-124	8.0	117	75
213-118	8.5	117	75
213-102	9.0	125	81
212-929	10.0	133	87
212-913	10.2	133	87
212-907	10.5	133	87
212-884	11.0	142	94
212-878	12.0	151	101
212-935	13.0	151	101

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.