



Dell Multifunction Printer - E515dw



A complete multifunction printer for easy, everyday printing

Boost office productivity with an easy-to-use 4-in-1 wireless¹ multifunction printer with essential productivity features for everyday printing tasks.

- Easily print, scan, fax and copy with features such as the automatic document feeder (ADF) and built-in duplexer for automatic two-sided printing.
- Get connected easily using the Dell Printer Easy Installer.
- Simplify printing tasks and maintenance with the Dell Printer Hub².

Simple set-up

Get your Dell printer up and running easily using the Dell Printer Easy Installer¹ and allow flexible connectivity with WiFi¹, Ethernet and USB connectivity options.

Designed for convenience

Scan or copy up to 35 sheets hands-free with the ADF and reduce paper use up to 50% using automatic two-sided printing.

Help simplify record keeping by copying both sides of an ID card on a single side of paper using the "ID Copy" button.

Print more with less interruptions using the optional high yield toner cartridge that prints up to 2,600 pages³ for greater savings. Minimize maintenance with the single fuser unit designed to last the life of the printer, and a cassette input paper tray that keeps paper dust-free.

Printing on-the-go

Print directly from compatible smartphones, tablets, and other mobile devices with the Dell Document Hub app, available on the App Store, Google Play and the Windows Store. The E515dw also supports AirPrint⁴, Google Cloud Print and Mopria, so you can print from virtually anywhere.⁵



One-stop solution to do more

Simplify your printing tasks and printer maintenance using Dell Printer Hub². This convenient, one-stop solution with an intuitive interface that integrates printer essentials and cloud connectivity for easy document management and control of your printer.

- 1-click to update printer firmware and software
- 1-click to execute customized scan shortcuts
- 1-click access to the Dell Document Hub cloud access solution, which also features cloud Optical Character Recognition to convert scans into editable, searchable files.

Receive automatic alerts when firmware and software updates are available, or when the toner runs low. Conveniently re-order toner via Dell Printer Hub.

Eco-conscious design

The E515dw meets the latest regulatory and environmental standards, including ENERGY STAR[®] qualification⁶ and Restriction of Hazardous Substances (RoHS) compliance⁷. It also supports printing on recycled, renewable content and chlorine-free paper.

Comprehensive services

Connect to technical support for any printing issues via phone or online during your standard 1-year Limited Hardware Warranty⁸, and enjoy 1-year Advanced Exchange⁹ after Remote Diagnosis Service¹⁰.

Stay covered longer when you choose optional 2-, 3-, 4-, or 5-year extended Limited Hardware Warranty⁸. Get dedicated support 24/7 with Dell ProSupport^{™11} service options.

[Learn more at Dell.com/printers](https://www.dell.com/printers)

Dell Multifunction Printer - E515dw

| | | |
|-------------------------------|--|--|
| Printer specifications | Printer type | Mono multifunction printer (Print, Copy, Scan, Fax) |
| | Print speed¹² | |
| | Simplex (600 x 600 dpi) | Up to 26 ppm (A4) |
| | Duplex (600 x 600 dpi) | Up to 13 ppm (A4) |
| | First page out time (simplex letter, 600 dpi) | From Ready state: as fast as 8.5 seconds From Power Saver mode: as fast as 17.5 seconds |
| | Print resolution | 600 x 600 dpi (Up to 2400 x 600 dpi) |
| | Operation panel | 2-line LCD screen |
| | Print language | |
| | Printer driver language | PCL 6, PostScript™ Level 3 Emulation, XPS |
| | Printer data stream | PCL 6, PostScript™ Level 3 Emulation |
| | Fonts | HP PCL® 6 Emulation: 66 scalable fonts, 12 bitmap fonts PostScript 3: 66 scalable fonts |
| | Processor speed | 266 MHz |
| | Memory, standard | 64 MB RAM |
| | Mobile printing support | Dell Document Hub (or Android, iOS and Windows 8 and later), AirPrint ⁴ , Google Cloud Print, Mopria-certified |
| Usage rate | Duty cycle | Up to 10,000 pages per month ¹³ |
| | Recommended monthly print volume | 300 - 1,000 pages per month |
| | | |
| Scan specifications | Scan type | Flatbed, ADF / Contact Image Sensor (CIS) |
| | Scan speed (Single-page document, 300 x 300 dpi) | Up to 17 ipm mono / up to 6 ipm color |
| | Scan resolution | 600 x 1200 dpi, up to 19200 x 19200 dpi (software enhanced) |
| | Scan depth | Color: 24-bit; Mono: 8 bit for gray scale |
| | Scan size (max) | Flatbed: 210 mm x 291 mm / ADF: 210 mm x 350 mm |
| | Scan to media (file format) | JPEG, TIFF, BMP, PDF, XPS |
| | Walk-up scan to | FTP (Network server), PC |
| Copy specifications | Copy speed (Single-page document, 600 x 600 dpi) | Up to 13 copes per minute (cpm) (A4) |
| | Maximum copies | 99 |
| | Enlarge | 25 to 400% |
| | Copy settings | Stack/Sort, N in 1 (2-in-1, 4-in-1), ID Copy (2-in-1), Autofit |
| Fax specifications | Fax transmission speed | Up to 33.6 Kbps |
| | Speed dial | Up to 200 entries |
| | Memory size | 8 MB |
| | Fax feature | Broadcast, Delay/Schedule, Priority, Secure, Forward |
| Paper handling | Input sources | Standard: 250-sheet input tray, single-sheet feeder Maximum: 251 sheets |
| | Automated Document Feeder (ADF) Specifications | |
| | Capacity | 35 sheets |
| | Media size | A4 Short Edge Feed (SEF), Letter SEF |
| | Types | Plain, Recycled |
| | Output destinations | Standard: 100-sheet bin Maximum: 100 sheets |
| | Standard tray | |
| | Types and weights supported | Plain Paper (60 - 80 g/m ²), Recycled paper |
| | Sizes | A4, A5, A5L, A6, US Letter, B5 (JIS), Executive, US Legal, Folio |
| | Single-sheet feeder | |
| | Types and weights supported | Plain Paper (60 - 80 g/m ²), Recycled paper, Thick Paper (80 - 105 g/m ²), Bond, Label, Envelope |
| | Sizes | A4, A5, A5L, A6, US Letter, B5 (JIS), Executive, US Legal, Folio, Com10, Monarch, C5, DL |
| | Duplexer | |
| | Types supported | 60 to 105 g/m ² , Plain, Thin, Thick, Bond, Recycled, Label, Envelope |
| | Sizes | A4, US Letter, B5 (JIS), A5, A5L, A6, Executive, US Legal, Folio |
| | Page layout options | Portrait or Landscape orientation, Multiple copies, Multi-page printing (N-up), Duplex printing (only for Windows and Mac Driver), Poster (only for Windows Driver), Watermarks (only for Windows Driver), Collate |
| | Printable area | 207.4mm x 347.1mm |

| | | |
|--------------------------------|--|--|
| Connectivity | Interfaces | USB 2.0 High Speed, Ethernet 10/100BASE-TX |
| | Wireless¹ | Wireless 802.11 b/g/n, WPA2.0 (Personal), WPS 2.0, WiFi Direct |
| Operating systems | | Microsoft® Windows® Server 2003 / Windows® Server 2003 x64 Edition Windows® Vista Windows® Server 2008 / Windows® Server 2008 R2 Windows® 7 Windows® 8/8.1 Windows® Server 2012 / Windows® Server 2012 R2 |
| | Windows | |
| | Macintosh | Apple Mac OS® X 10.7x, 10.8.x, 10.9.x, 10.10x |
| | Others | RedHat Enterprise Linux Desktop 6 (x32/x64) SUSE Linux Enterprise Desktop 11 (x32/x64) Ubuntu 12.04 LTS (x32/x64) |
| Physical specifications | Printer dimensions (W x D x H) | 409 mm x 398.5 mm x 316.5 mm |
| | Printer weight | 11.5 kg (with consumables) |
| | Shipping dimensions (W x D x H) | 623 mm x 517 mm x 499 mm |
| | Shipping weight | 15.6 kg |
| | Operating environment | Temperature: 10°C to 32.5°C; Relative Humidity: 20% to 85% RH, non-condensing; Altitude: <2,000 m |
| | Storage (packaged) | Temperature: 0°C to 35°C; Relative Humidity: 10% to 80% RH; Altitude: <2,000 m |
| | Acoustics (Pressure - LpAM / Power - LwAd)¹⁴ | Printing (simplex): 50.0 dB / 6.5 B Standby: 33 dB / 4.6 B |
| Power specifications | Voltage | 230 vac models: 220 to 240 vac, 50 Hz / 60 Hz nominal |
| | Power consumption | Printing mode: 480W (230 vac model) Standby mode: < 60W (230 vac model) Power Saver mode (Sleep): ≤ 6.6W (230 vac) |
| Consumables | Ship-with toner capacity³ | Up to 700 capacity (Black) |
| | Standard toner capacity³ | Up to 1,200 page capacity (Black) |
| | High-yield toner capacity³ | Up to 2,600 page capacity (Black) |
| | Imaging drum | Up to 12,000 pages |
| Product certifications | Safety and EMC: UL/cTUVus, FDA, CB, CE, R&TTE, C-tick, A-Tick, Nom, Semko, ICASA, IEC60650-1, CIPSR22, 24, FCC, VCCI Others: ErP Lot 6 Tier 2 (2013), ErP Lot 4 (2012), RoHS-compliant ⁷ , ENERGY STAR® v2.0 ⁶ , WEEE, ErP Lot 26 Tier 1 and Tier 2 | |
| Supported languages | English, French, German, Italian, Spanish, Danish, Norwegian, Dutch, Swedish | |
| Printer management | Dell Printer Hub, Dell Open Print Driver (OPD), Dell OpenManage Printer Manager v2 (OPPM), Standard Printer MIB | |
| Contents in box | Dell Multifunction Printer - E515dw, Software and Documentation CD, Ship-With Black Cartridge (700 page yield ³), Power Cord, USB Cable, RJ11 Cable, Setup Guide | |

Available consumables



Dell E310/514/515 series Black Toner Cartridge, 1,200 page yield⁷



Dell E310/514/515 series High Yield Black Toner Cartridge, 2,600 page yield⁷



Imaging drum, up to 12,000 pages

1. For wireless printing information, please refer to dell.com/support/wireless_printing
2. Supports Windows 7, 8 and later only.
3. Toner yield based on testing in accordance with ISO/IEC 19752. Yields vary with usage and environmental conditions.
4. AirPrint-enabled printers work with iPad, iPhone (3GS or later), and iPod touch (3rd generation or later) running iOS 4.2 or later.
5. The printer and the mobile device must be connected on the same network.
6. For details on energy efficiency of ENERGY STAR® qualified products, refer to: www.energystar.gov.
7. Meets the requirements of the EU RoHS Directive 2011/65/EU on the Restriction of the use of certain Hazardous Substances (RoHS).
8. For a copy of Limited Hardware Warranty, write Dell Products, Dell House, The Boulevard, Cain Road, Bracknell, Berkshire, RG12 1LF, UK or see dell.com/warranty. For warranty information for other countries, see website: dell.com/servicecontracts and then select the country.
9. Replacement system or replacement part will be dispatched, if necessary, following phone-based troubleshooting, in advance of receipt of returned defective part or system. Replacements may be refurbished. Defective unit must be returned. Availability varies. Other conditions apply.
10. Remote Diagnosis is determination by online/phone technician of cause of issue; may involve customer access to inside of unit and multiple or extended sessions. If issue is covered by Limited Hardware Warranty and not resolved remotely, technician and/or part will be dispatched, usually within 1 business day following completion of Remote Diagnosis. Availability varies. Other conditions apply.
11. Availability and terms of Dell Services vary by region. For more information, visit Dell.com/servicecontracts/global. Subject to parts availability, geographical restrictions and terms of service contract. Service timing dependent upon time of day call placed to Dell. Defective unit must be returned.
12. Actual print speed may vary with use. Measured in accordance with ISO/IEC 24734 methodology.
13. Duty cycle is defined as the maximum number of imaged outputs a device could deliver in a month. This metric provides a comparison of robustness in relation to other Dell printers and multifunction printers.
14. Tested in accordance with ISO 7779 and reported in accordance with ISO 9296. Acoustics - Declared noise emission values of computer and business equipment.

©2015 Dell Corporation Limited. Dell, the Dell logo and Dell Toner Management System are registered trademarks or trademarks of Dell Inc. Other trademarks and trade names may be used in this document to refer to either the entities claiming the marks and names or their products. Dell disclaims proprietary interest in the marks and names of others. Microsoft, Windows and Windows NT are registered trademarks or trademarks of Microsoft Corporation. Android and Google Cloud Print are registered trademarks of Google Inc. iPad, iPhone, iPod, and iPod touch are trademarks of Apple Inc., registered in the U.S. and other countries. AirPrint and the AirPrint logo are trademarks of Apple Inc. Dell Products, Dell House, The Boulevard, Cain Road, Bracknell, Berkshire, RG12 1LF, UK. Product availability varies by country. Please contact your Dell representative for more information.

Specifications are subject to change without notice. Dell cannot be responsible for errors and omissions in typography or photography.

