

SIEMENS

Product data sheet

6SL3224-0BE17-5UA0

| | |
|--|---|
| product name | PM240 IP20 FSA U 400V 0,75kW |
| Design | A |
| Back supply / [nicht versorgt - möglich] | No |
| rated output / kilowatt (kW) | 0.75 kW |
| rated output / in Horse Power (HP) | 1 hp |
| Input voltage / minimum | 380 V |
| Input voltage / maximum | 480 V |
| Line frequency | 50 Hz |
| efficiency eta | 95 |
| Rated Input Current | 2.6 A |
| Output current / for constant torque / rated value | 2.2 A |
| Phase number / of the outputs | 3 |
| Electrical output frequency / maximum | 650 Hz |
| type / [nicht versorgt - der Überlastbarkeit] | 150% for 57s with 300s, 200% for 3s with 300s |
| Protection class IP | IP 20 |
| Depth | 0.145 m |
| Height | 0.173 m |
| Width | 0.073 m |
| weight | 1.1 kg |
| Type of cooling | fan |
| cooling method / [nicht versorgt - Kühlkörper] | Aluminium |
| letzte Änderung: | Oct 25, 2010 |