

Datasheet

PVC Test lead wire 2.5mm²



Image representative

Product Description

Reference Standard

Customer's sample spec.and the general standard

Multi-construction

Single

Cable Construction

Conductor

Bare Copper

Cross section

2.5mm²

Construction(±0.003mm)

0.08× 498

Standard Dia.

2.06

Jacket

PVC

Thickness


0.85

Jacket Dia.(mm)

3.90±0.15

Color

Red(RAL3000); Black;
Blue(RAL5015); Yellow(RAL1021)
Green(RAL6032)



Electrical Characteristics

Max.Conductor DC Resistance at 20 °C (Ω /Km)	7.43
Min.Insulation DC Resistance at 20 °C (M Ω *Km)	>500
Rated Temperature(°C)	-20~+80
Rated Voltage (V)	300/500

Color	Product code	RS PART NO.
Red	#3709	7481976
Black	#3710	7481970
Blue	#3711	7481989
Yellow	#3712	7481982
Green	#3713	7481986