

# Product information

## JIGSAW 18V LXT



Satisfying the professional's needs

### DJV180Z

Battery Type	Lithium-ion
Body only machine	1
Voltage	18 v
Max in steel	10 mm
Max in wood	135 mm
Strokes per Minute	0-2600 spm
Stroke Length	26 mm
Noise sound pressure	78 dB(A)
Noise K factor	3 dB(A)
Vibration K factor	1.5 m/sec <sup>2</sup>
Vibration: Cutting Chipboard	8 m/sec <sup>2</sup>
Vibration: Cutting Sheet Metal	3.5 m/sec <sup>2</sup>
Net weight	2.8 kg



**STANDARD EQUIPMENT:** 194204-5 18V Li-ion battery, 417853-4 Vacuum Head Sets - Dust Nozzle, 783202-0 HEX WRENCH  
4

- Tool-less blade change.
- 22 minute charge time with the air cooled Makstar Optimum Charging System.
- Lithium-ion batteries have greater life spans than their Ni-MH or Ni-Cad counterparts giving 430% greater run time.
- Lithium-ion's 40% weight saving means 18 volt power can be obtained by a battery that weighs the same as a 12 volt Ni-MH battery.
- High comfort grips.
- LED job light that creates an easy to trace cutting line.
- Smooth and powerful cutting at the high stroke speed of 2,600spm.

Details correct as of: 17-6-2014

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

[www.makita.com](http://www.makita.com)