

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION







© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.



LOC
ESDIST
00

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED ECR-07-000873	16JAN07	C.Z	S.Y

4 Pos.
(SCALE 4-1)

5~15 Pos.



3 Pos.




2 Pos.

7-292253-5	5-292253-5	3-292253-5	1-292253-5	15	28	31.8	25.2	31.0
7-4	5-4	3-4	1-4	14	26	29.8	23.2	29.0
7-3	5-3	3-3	1-3	13	24	27.8	21.2	27.0
7-2	5-2	3-2	1-2	12	22	25.8	19.2	25.0
7-1	5-1	3-1	1-1	11	20	23.8	17.2	23.0
7-0	5-0	3-0	1-0	10	18	21.8	15.2	21.0
6-9	4-9	2-9	0-9	9	16	19.8	13.2	19.0
6-8	4-8	2-8	0-8	8	14	17.8	11.2	17.0
6-7	4-7	2-7	0-7	7	12	15.8	9.2	15.0
6-6	4-6	2-6	0-6	6	10	13.8	7.2	13.0
6-5	4-5	2-5	0-5	5	8	11.8	5.2	11.0
6-4	4-4	2-4	0-4	4	6	9.8	3.2	9.0
6-3	4-3	2-3	0-3	3	4	7.8	—	7.0
6-292253-2	4-292253-2	2-292253-2	292253-2	2	2	5.8	—	5.0
BLACK	YELLOW	BLUE	NATURAL	Pos.	A	B	C	D

PART NO.

NOTES:


- MATERIAL: HOUSING - NYLON 66 (UL94V-0)
POST - TIN BRASS
- APPLICABLE RECEPTACLE P/N 173977
- THIS PART HAS BEEN OBSOLETE.

RECOMMENDABLE PCB LAYOUT
(PCB THK:0.8-1.6)

TOLERANCES UNLESS OTHERWISE SPECIFIED:

10 > * : ±0.2
30 > * > 10 : ±0.25
100 > * > 30 : ±0.3
ANGLE : ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MMMATERIAL
SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

FINISH
SEE NOTE

DWN 31JAN03

CHK 31JAN03

S.YAO

APVD 31JAN03

T. SASAKI

PRODUCT SPEC

108-60016

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics Corporation
SHANGHAI, CHINA

NAME

POST HEADER ASS'Y HORIZONTAL TYPE
(AMP CT CONNECTOR 2mm PITCH)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=292253

SCALE

5:1

SHEET

1 OF 1

REV

A