

SPECIFICATION SHEET



TOPICA 200 & 450 PLUG IN TIMESWITCH

<u>PRODUCT</u>	<u>DIAL TYPE</u>	<u>SWITCHING CAPACITY</u>
Tactic STA200BP	24 HOUR	13 Amps
Tactic 450S	7 DAY	13 Amps

Grasslin's synchronous plug-in timer product range. Captive tappets allow programming of a routine switching sequence. The product is available in 24 hour or seven day versions. Only for indoor use, to control any appliance with a BS1363 plug fitted with a BS1362 fuse. If in doubt, consult a qualified electrician. Suitable for all loads rated up to 13A at 230VAC

Technical specification:

AC switching capacity:	
- resistive load	13A 250v AC
- inductive load cos ϕ 0.6	8A 250v AC
- incandescent lamp load	1350W
- flourescent lamp load	60W
- Ambient temperature	-20°C to +40°C
- Accuracy	typically \pm 2.5 sec. / day
Minimum switching time	
- Topica STA200BP	15 minutes
- Topica 450S	2 hours
- Manual override	fix ON / Timed / fix OFF (advance is self- resetting)

IMPORTANT

Not suitable for radiant heat type electric fires as close proximity to flammable materials could cause fire. Do not use for immersion heater control. There is a hard wire timer available from Grasslin conforming to BEAB regulations which is suitable for this application.

IMMERSION HEATER MODELS AVAILABLE

IHT GPT	24 hour
IHT GPW	7 day
IHT DIGI	24 hour / 7 day DIGITAL

