





LOC	DIST	REVISIONS			
		P	LTR	DATE	APVD
FT	0		M	REVISED PER 0G3B-0164-05	3/8/05
				SS	GS

D

C

B

A



RECOMMENDED PC BOARD LAYOUT

- 1 NYLON, UL 94V-0 RATED, RED.
- 2 BRASS PER ASTM B36.
- 3 3.81μm [.000150] MIN TIN OVER 2.54μm [.000100] MIN COPPER.
- 4 0.76μm [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81μm [.000150] MIN TIN FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27μm [.000050] MIN NICKEL.
- 5 3.81μm [.000150] MIN LEAD FREE TIN OVER 2.54 μm [.000100] MIN COPPER.
- 6 0.76μm [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81μm [.000150] MIN LEAD FREE TIN FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27μm [.000050] MIN NICKEL.

6	YES	1-207441-0
6	NO	207441-9
5	NO	207441-8
5	YES	207441-7
4	NO	207441-4
4	YES	207441-3
3	NO	207441-2
3	YES	207441-1
CONTACT FINISH		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
HOUSING: 1
CONTACT: 2

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	0.25 [.010]
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-

DWN
L.SIPE
CHK
R.STONE
APVD
A.TRAVIS
PRODUCT SPEC
APPLICATION SPEC

03/10/92
3-17-92
3-17-92

108-10033

WEIGHT
-

CUSTOMER DRAWING

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

PIN HEADER ASSEMBLY,
9 POSITION, METRIMATE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=207441

RESTRICTED TO
-

SCALE
4:1

SHEET
1

OF
1

REV
M