

# Surface Socket Outlets

## 332RS6W

### General Information

---

<b>Extended Product Type:</b>	332RS6W
<b>Product ID:</b>	2CMA167180R1000
<b>EAN:</b>	7392696671804
<b>Catalog Description:</b>	Surface socket-outlet, 6h, 32A, IP67, 3P+E
<b>Long Description:</b>	Surface socket-outlet, earthing sleeve position 6h, rated current 32A, IP67 watertight, 3-poles+earth, frequency 50-60hz color code Red

---

### Ordering

---

<b>EAN:</b>	7392696671804
<b>Minimum Order Quantity:</b>	1 piece
<b>Country of Origin:</b>	Sweden (SE)

---

### Dimensions

---

<b>Product Net Width:</b>	99 mm
<b>Product Net Height:</b>	178 mm
<b>Product Net Length:</b>	129 mm
<b>Product Net Weight:</b>	0.43 kg

---

### Container Information

---

<b>Package Level 1 Width:</b>	144 mm
<b>Package Level 1 Length:</b>	202 mm
<b>Package Level 1 Height:</b>	140 mm
<b>Package Level 1 Units:</b>	1 piece

---

### Environmental

---

<b>RoHS Status:</b>	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
---------------------	--

---

### Certificates and Declarations (Document Number)

---

<b>Declaration of Conformity - CE:</b>	<a href="#">2CMC700005D0001</a>
<b>Environmental Information:</b>	<a href="#">2CMC700001D0002</a>
<b>RoHS Information:</b>	<a href="#">2CMC700022</a>

---

### Additional Information

---

<b>Additional Information:</b>	Cable entry Ø 25mm
<b>Cable Cross-Section:</b>	2.5 ... 10 mm <sup>2</sup>
<b>Color:</b>	Red
<b>Degree of Protection:</b>	IP67
<b>Enclosure Material:</b>	Thermoplastic polyester (PBT)
<b>Frequency (f):</b>	50 Hz 60 Hz

<b>Function:</b>	Surface socket outlet
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Invoice Description:</b>	Ind. P&S#332RS6W
<b>Number of Poles:</b>	4
<b>Product Main Type:</b>	RS
<b>Product Name:</b>	Industrial Socket Outlet
<b>Protection Type:</b>	Watertight
<b>Rated Current (I<sub>n</sub>):</b>	32 A
<b>Rated Voltage (U<sub>r</sub>):</b>	380 ... 415 V
<b>RoHS Date:</b>	2009-01
<b>Standards:</b>	IEC 60309-1,-2

---

## **Classifications**

---

<b>E-nummer:</b>	2416555
<b>UNSPSC:</b>	39120000

---