






solder pot position:



harnessing dimensions for
cable RG 58CU, RG 141AU



Cramping tool of outer conductor:
hand tool: 09 99 000 0503 00
die: 09 99 000 0515 00
cavity A

					Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	Male coaxial contact, 50 Ω, straight cable termination inner conductor for solder termination outer conductor for solder or crimp termination	Maßstab/ Scale 5:1	
			Detail.	29/09/04	TR					
			Insp.							
			Stand.							
32486	13/12/04	TR	HARTING EURL F-95972 Paris						TB 09 69 281 X143	Blatt/ Page 1 / 1
32233	29/09/04	TR								
Mod.	Dat.	Name								