

4		3		2		1																			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION																					
COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.																									
AMP WIRE RANGE 16-14 AWG STRANDED FILE E66717 16-14 AWG STRANDED LR7189 Certified 16-14 AWG STRANDED				LOC G DIST 86 REVISIONS <table><thead><tr><th>F</th><th>LTR</th><th>DESCRIPTION</th><th>DATE</th><th>DWN</th><th>APVD</th></tr></thead><tbody><tr><td>C</td><td></td><td>REV PER 0G3A-0556-03</td><td>08SEP03</td><td>JR</td><td>TM</td></tr></tbody></table>				F	LTR	DESCRIPTION	DATE	DWN	APVD	C		REV PER 0G3A-0556-03	08SEP03	JR	TM						
F	LTR	DESCRIPTION	DATE	DWN	APVD																				
C		REV PER 0G3A-0556-03	08SEP03	JR	TM																				
1				1 MARKED AMP 16-14 2 DESIGNED FOR WIRE INSULATION DIA OF .115-.160. 3 BODY: .016±.001 THK BRASS, TIN PL. SLEEVE: NYLON, BLUE 4 RATED FOR 15 MAX AMPERE 5 PRELIMINARY - NOT FOR PRODUCTION																					
TYCO ELECTRONICS CUSTOMER SERVICE SYSTEM <table><tr><td>FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWING AND TECHNICAL DOCUMENTS</td><td>PRODUCT INFORMATION CENTER 1-800-522-6752</td></tr><tr><td>FOR APPLICATION TOOLING INFORMATION</td><td>TOOLING ASSISTANCE CENTER 1-800-722-1111</td></tr><tr><td>FOR ORDER ENTRY</td><td>1-800-526-5142</td></tr></table> MAX. RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F] VOLTAGE RATING: 300V MAX CIRCULAR MIL AREA: 2,050-5,180 STRANDED THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: INCHES TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC + - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± - MATERIAL: - 3 FINISH: - 3				FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWING AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	FOR ORDER ENTRY	1-800-526-5142	<table><tr><td>100</td><td>LOOSE PIECE</td><td>8-696369-1</td></tr><tr><td>4000</td><td>ON TAPE</td><td>5 696369-2</td></tr><tr><td>1000</td><td>LOOSE PIECE</td><td>696369-1</td></tr><tr><td>QTY</td><td>PACKAGE TYPE</td><td>PART NO.</td></tr></table> DRN JR RUTH CHK T MICHELUTTI APVD T MICHELUTTI PRODUCT SPEC APPLICATION SPEC 114-13076 WEIGHT CUSTOMER DRAWING DATE 08DEC01 DATE 08DEC01 DATE 08DEC01 NAME SIZE CAGE CODE DRAWING NO RESTRICTED TO Tyco Electronics Corporation Harrisburg, PA. 17057 TAB, 250 SERIES, FASTON, PIDG, WIRE: 16-14 AWG A3 00779 C-696369 SCALE 4:1 SHEET 1 OF 1 REV C				100	LOOSE PIECE	8-696369-1	4000	ON TAPE	5 696369-2	1000	LOOSE PIECE	696369-1	QTY	PACKAGE TYPE	PART NO.
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWING AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752																								
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111																								
FOR ORDER ENTRY	1-800-526-5142																								
100	LOOSE PIECE	8-696369-1																							
4000	ON TAPE	5 696369-2																							
1000	LOOSE PIECE	696369-1																							
QTY	PACKAGE TYPE	PART NO.																							
AMP 1470-19 REV 31MAR2000																									
14MAR01 9:17am omp13469				H:\u.kst\696369_1-c.dwg																					