


FILE NO:

DESCRIPTION CONTROL

REV	DESC	DATE	ECN NO
C		2012.06.15	N21206115
D		2012.11.30	N21212013



RoHS COMPLIANT

* 330010021674	LABEL:"HSYNC"15*20MM		1	PCS	* 330010021499	LABEL:"7587517"45*25MM	1	PCS
* 330010021675	LABEL:"VSYNC"15*20MM		1	PCS	* 390	TIE-A-BK	120*1	MM
* 330010021638	LABEL:"7587517"30*40MM		1	PCS	* 390	CARTON:46*30*20CM	A/R	PCS
12	120010000031	PVC-BK10/50	37	G	* 390	PE BAG:30*28*0.08MM	A/R	PCS
11	240010200050	SRW-Q39.6/BK10	2	PCS	* 390	PE BAG:7*10*0.06MM	1	PCS
10	240040000034	ID4.2*12.7MM	5	PCS				
9	210010000337	FDIL-CU-32MM	55*1	MM	OUTER MOLDING	AHD1556	AV-BNC012	SR013
8	210030000062	HI TEAMP TAPE:W:24MM	70*1	MM	INNER MOLDING	AHD1514		
7	120020000001	PE-5321	3.9	G				
6	210040000034	TAPE:W:12MM	40*1	MM				
5	200032000157	TUBE-HT-Ø2.0	6*5	MM				
4	100500126021	JUMP WIRE:26#-UL1007	35*3	MM				
3	110121301038	BNC-PLUG-Ø9.5(75Ω)ID:2.6MM	5	PCS				
2	104-1510120010X-C	CDS-H15P(BK)/-9	1	SET	DRAWN BY: 向三茶	SCALE: NONE	DATE: 2011.06.13	REV D
1	12067051100051	UL2919-5C DAX*28#(U1354)+A+D+B-BK10-Ø9.0(75OHM)	2.0	M	CHECKED BY:	CUSTOMER: C331	PAGE: 1/1	
					APPROVED BY:	CUSTOMER P/N: 7587517		
NO	PART NO.	DESCRIPTION	QTY	UNIT	ALL DIMENSIONS IN mm (UNLESS OTHERWISE SPECIFIED)			

PIN ASSIGNMENT
HD15<MALE> BNC<MALE>