

Product Information



AA23POI050B10-11x20

EAN 4031582317534

Swivel castor with intermittend brake, housing made of Polypropylene, stem with circlip.

Wheel centre made of Polypropylene, plain bearing

Technical Data	
Wheel diameter	50 mm
Width of Tread	8 mm
Castor width	55 mm
Metal stem with circlip	11 x 20 mm
Swivel Interference	98 mm
Overall height	58 mm
Temperature	- 10 / + 40 °C
Weight	0.097 kg
Swivel Radius	49 mm
Hardness of tread	D 65 Shore



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

Product Information



AA23POI050B10-11x20

EAN 4031582317534

