


Affordable All-in-One for the home office.
Print, copy, scan and fax.

Office Range



The PIXMA MX300 is an affordable solution for home office convenience to print, copy, scan and fax. Fast printing with 22ppm black and 17ppm colour. High resolution and microscopic ink dots ensure you produce quality documents and photos. Scan at up to 600 x 1200 dpi. The PIXMA MX300 is a versatile and affordable All-in-One solution for the home office.



Key Features

As a Printer

- High quality photos and documents with 2 picolitre FINE print head technology and 4800 x 1200 dpi¹
- Fast document printing up to 22ppm in black and 17ppm in colour³
- Photo lab quality prints delivered in high speeds of approx 46 seconds³
- Direct photo printing using PictBridge⁴
- Borderless printing up to A4⁵

As a Copier

- Faithfully reproduce copies as they are seen with the naked eye with Dual Colour Gamut Processing Technology
- Standalone copying without a computer
- Copy up to 22cpm black and 17cpm colour³

As a Scanner

- Scan high-quality photos and documents at up to 600 x 1200 dpi

As a Fax

- Supports the Super G3 standards up to 33.6kbps to enable plain paper colour faxes and PC faxes to be transmitted
- No need to worry if the ink or paper runs out while receiving a fax, high-capacity memory can store data for up to 50 pages
- Speed dialling allowing up to 20 numbers to be registered

Easy to use Software – Just 3 easy steps

- Easy-Photo Print EX produces optimised prints of both portraits and sceneries with Auto Image Fix technology

4800^{Maximum}
2^{Minimum}
pi

ChromaLife100

22 17
Black Color
ppm

FAX
33.6Kbps

SCAN
600x1200dpi

FINE Cartridge

PictBridge

Quick Start

Quality images

4800 x 1200 dpi resolution and 2 picolitre FINE print-head technology for high quality photos and documents¹

Long Lasting Prints

Produce long lasting printed photos with a combination of Canon's genuine dye ink and genuine photo papers²

Fast Printing and Copying

Print and copy at up to 22ppm black and 17ppm in colour³

Professional Fax

Enables stand-alone plain paper colour faxes and PC faxes to be transmitted

Quality Scanning

Scan high-quality photos and documents at up to 600 x 1200 dpi

FINE Cartridge

integrated print head and ink allows the cartridges to be replaced with a single touch

Click-Connect-Print

Print photos directly from compatible digital cameras using PictBridge technology, no need for a PC⁴

Quick Start

Quick Start feature allows operations virtually the moment the power is turned on



PIXMA – Print with Confidence

Canon's PIXMA range features FINE print-head technology which places microscopic ink droplets on the page with unparalleled accuracy and consistency. PIXMA delivers superior quality to photographic and document printing with unsurpassed speed and reliability.

PIXMA MX300

All-in-One Inkjet Printer

Canon
advanced simplicity®

PIXMA MX300 Technical Specifications

Printer Functions		
Min. Ink Droplet Size ¹	2 picolitres	
Printing Resolution ¹	4800 x 1200 dpi	
Print Speed ³	Black Text : Up to 22ppm, Colour Text & Graphics : Up to 17ppm, 6"x4" Standard Borderless Photo : Approx. 46 secs	
Ink Cartridges	PG-40, CL-41 (optional PG-50, CL-51 or PG-37, CL-38)	
Ink Yield*	Borderless 6x4" photo	PG-40 (approx. 2760), CL-41 (approx. 126) or PG-50 (approx. 5310), CL-51 (approx. 204)
	Plain paper A4	PG-40 (approx. 329), CL-41 (approx. 312) or PG-40 (approx. 510), CL-41 (approx. 545)
Borderless Printing	6"x 4", 5"x 7", 8"x10", Letter, A4, Credit Card, Wide	
Plain Paper Capacity	100 sheets	
Supported Paper Sizes	A4, Letter, Legal, A5, B5, Envelopes(DL, COM10), 4"x6", 4"x8", 5"x7", 8"x10", Credit Card (54mm x 86mm)	
Supported Paper Weights	Plain Paper: 64-105g/m². Canon specialty paper (max paper weight): approx 273g/m² (Photo Paper Plus Double-sided)	
Paper Types	Plain Paper	Plain Paper Super White Paper (SW-201) High Resolution Paper (HR-101)
	Photo Paper	Photo Paper Plus Glossy (PP101) Photo Paper Plus Glossy II (PP201) Photo Paper Plus Double Sided (PP101D) Glossy Photo Paper (GP401 & GP501) Photo Paper Pro (PR101) Matte Photo Paper (MP101) Semi-Gloss Photo Paper(SG201)
	Other	T-shirt Transfers (TR301) Glossy Photo Stickers (PS101) Envelopes (DL, Com#10)
Camera Direct Printing ⁴	PictBridge	
Mobile Phone Printing ⁴	PictBridge	
Copier Functions		
Speed	Black Text : Up to 22ppm, Colour Text & Graphics : Up to 17ppm	
Multiple Copy	Up to 99 copies	
Reduction/Enlargement	25% to 400%	
Special Copy Functions	Fit-to-page	
Scanner Functions		
Scanner Type	CIS	
Scanning Resolution	600 x 1200 dpi	
Special Scanning Functions	Push Scan	
Fax Features		
Transmission Speed (Mono)	Approx. 3 sec. (33.6kbps)	
Modem Speed	Super G3 standards up to 33.6kbps	
Fax Memory	Approx. 50 pages	
Speed Dials	20 locations	
PC Faxing (Windows only)	N/A	
General Features		
PC Interface Type ⁶	USB 2.0 Hi-Speed	
Operating System	PC: Windows Vista/XP/2000, Mac: OS.X (10.2.8 or later)	
Included as Standard	PIXMA MX300 All-in-One printer, Setup CD-ROM and printed documents, PG-40 FINE black cartridge, CL-41 FINE colour cartridge, sample photo paper, telephone line cable, power cord and 12 month warranty card	
Software Included	Easy-PhotoPrint EX, MP Navigator EX, ScanSoft OmniPage SE and Presto! Page Manager	
Power Source	AC 100-240V, 50/60Hz	
Power Consumption	Max: 21W (copying), Standby: 4.5W	
Min. Dimensions (W x D x H)	465 x 440 x 174 mm	
Weight	Approx. 7kg	

Disclaimers

- Ink droplets can be placed with a pitch of 1/4800 inch at minimum.
- Up to 100 Years' Life in a Photo Album when printed with ChromaLife100 ink on selected Canon photo papers. Kept in a photo album, shut out light and air (gas), temperature 23 degrees and 50% humidity. Predicted value from the accelerated test. Result may vary based on individual environmental factors. For more information, please visit canon.com.au/ChromaLife100
- Print and copy speed dependent on system configuration, image/document complexity, type of paper used, software, print mode and does not take into account data processing time on host computer.
- PictBridge camera direct and mobile phone printing requires PictBridge compatible digital cameras and phones in order to function. Check with your manufacturer or users guide to determine PictBridge compatibility.
- Supported paper types for borderless printing: Photo Paper Pro, Photo Paper Plus Glossy, Photo Paper Plus Glossy II, Photo Paper Plus semi-gloss, Glossy Photo Paper, Matte Photo Paper, Photo Paper Plus Double-sided
- USB 2.0 Hi-Speed performance requires Windows Vista, Windows XP with Service Pack 1 or Windows 2000 with Service Pack 4 with pre-installed USB 2.0 Hi-Speed port.

* Ink yield calculation is based on printing Canon 24 standard digital images on Photo Paper Plus Glossy (6" x 4" borderless print) with default settings in Windows XP driver and printing on Plain Paper (A4-ISO/IEC 24712). The figure above is an average value, measured when printing continuously using the ink immediately after it is unsealed, until the ink is out. Ink yield may vary depending on photos/documents printed, applications software used, print mode and type of paper used. This should be used as a guide only and does not take into account ink that might be used for head cleaning or head refreshing to maintain printer performance. Please visit our website for further details.

Subject to change without notice



Consumables



Included



Optional

canon.com.au