



Shower Flow Control - Hot or cold - Adjustable time and flow delay.

GENERAL INFORMATION

Pattern No. key :CP = Chrome Plate

Size	Pattern No.	Box Qty	Code	Barcode
1/2	890-2	1	344007	5013866078866

DIMENSIONS (mm)

Code	Description	A	B
344007	890-2 SELF CLOSING SHOWER FLOW CONTROL	1/2" BSP	1/2" BSP

PRESSURE & TEMPERATURE

890-2 Exposed Shower	Minimum Operating Pressure (bar)	Maximum Cold Working Pressure (bar)	Maximum Hot Working Pressure (bar)
1/2 890 CP EXPOSED SHOWER FLOW CONTROL	0.2 bar	3.0 bar at temperatures up to 60oC	Not Suitable for Maximum Hot Working Pressure

CARE & MAINTENANCE

Care

To maintain the surface finish, simply wipe occasionally with a mild detergent on a soft damp cloth. Dry, using a soft cloth. Never use abrasive cleaners or chemical household cleaners and avoid contact with concentrated bleach.

Maintenance

No regular maintenance is required for this product.

In case of complete replacement Pegler recommend service valves should be fitted to the supply inlets.

For any further help or replacement parts please contact the Service Support Team on 0800 1560050.

REGULATIONS

Regulations

It is important to ensure that the water supplies to your taps and mixers are connected in accordance with the water regulations (WRAS) requirements and good plumbing practice.

If the water flow streams are separate all the way to the outlet of the fitting, then there is no requirement to fit check valves to the cold and hot pipes even if the supply pressures are unbalanced.

It is recommended that in all new and refurbishment installations a thermostatic mixing valve should be installed on the hot inlet supply. The thermostatic mixing valve is designed to prevent scalding when using the hot water supply.

GUARANTEE

Luxury Taps and Mixers

Pegler Yorkshire Customcare 5 Year Guarantee - Terms and Conditions

Product are subject to a 5 year guarantee that is between Pegler Yorkshire and the final purchaser of the product.

The guarantee is subject to proof of purchase being supplied.

This guarantee does not affect any statutory rights the consumer may have in law.

The guarantee covers manufacturing or material defects and does not cover parts subject to normal wear and tear.

This product has been designed for the use of homeowners and domestic users and therefore the guarantee is subject to products being fitted in domestic circumstances such as UK housing stock.

Finishes other than chrome are covered for a period of 3 years only and the guarantee on the finish is subject to the cleaning instructions being followed.

The guarantee is not applicable where the product is fitted contrary to the conditions in the fitting instructions.

Abusive behaviour and accidental damage to the product are not covered by this guarantee.

The extent of this liability is limited to the cost of the replacement of the defective item and not to fitting or consequential damages.