

General Information

Extended Product Type:	M120/35.FF
Product ID:	1SNA115146R1500
EAN:	3472591151466
Catalog Description:	M120/35.FF
Long Description:	- Compact two stud terminal block, - Lug mounting in accordance with NF C 20-130 and DIN 46234, - Various marking options, - Rail or base mounting.

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Solution Series

Ordering

Color:	Grey
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160020C0201
Instructions and Manuals:	1SNC160020C0201

Dimensions

Product Net Width:	35 mm
Product Net Height:	69 mm
Product Net Depth:	51 mm
Product Net Weight:	130 g

Technical

Rated Cross-Section:	70 mm ²
Spacing:	35 mm
Connection Type:	Stud
Function:	Feed-through
Number of Levels:	1
Connecting Capacity Main Circuit:	Stud / Flexible 1x 2.5 ... 70 mm ² Stud / Rigid 1x 2.5 ... 70 mm ²
Rated Current (I _n):	Main Circuit 192 A
Rated Short-time Withstand Current (I _{cw}):	for 1 s 8000 A
Rated Voltage (U _r):	1000 V
Pollution Degree:	3
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Tightening Torque:	Cable Lug 12 N·m

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Connecting Capacity UL/CSA:	Stranded 250 AWG

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
RoHS Status:	Following EU Directive 2011/65/EC

Certificates and Declarations (Document Number)

cUL Certificate:	1SND165000A0203
Declaration of Conformity - CE:	1SND225011U1000
EAC Certificate:	1SND161009A1100
RoHS Information:	1SND230022F0204

Classifications

Object Classification Code:	X
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	135 mm
Package Level 1 Length:	175 mm
Package Level 1 Height:	74 mm
Package Level 1 Gross Weight:	1.3 kg
Package Level 1 EAN:	3472591151466
Package Level 2 Units:	80 piece
Package Level 2 Width:	300 mm
Package Level 2 Length:	500 mm
Package Level 2 Height:	150 mm
Package Level 2 Gross Weight:	21.3 kg
Package Level 3 Units:	3840 piece
Product Packing Type:	Box

