

**Product Name:** 10wp Flexi PV Solar Panel Kit

**Part Number:** SFP010

**Photo Filename:** 10wp Flexi PV Solar Panel Kit

- Super tough and powerful flexible solar panel
- Crystalline cell for maximum energy per sq metre
- Fully weather sealed system – even against salt water
- Ideal for deck tops, caravan roofs and camper vans
- In built diode prevents battery discharge
- 2 year panel warranty and 20 year cell performance warranty\*

**Catalogue Description:** The Flexi PV range of is a tough, fully weather resistant flexible solar panel designed for use in the harshest environmental conditions. Suitable for permanent fixing or stand alone use, the 10wp Flexi PV kit is ideal for battery maintenance, camping / caravanning, electric fence power and many more applications

**Technical Description:**

The kit comprises:

1 x SFP010 – 10wp solar panel with pre-wired 4m cable

2 x Croc clips

1 x Fuse

6 x Ring Terminals

1 x Fitting Instructions

The typical Daily performance of the solar panel in peak conditions: 4.41amp-hours per day

Panel Size – 357x268x2mm

Panel Weight – 0.4kgs

**\*Cell performance warranty states that at 20 years the cell output will be no less than 80% of new performance values – i.e the cell degradation rate will be no greater than 20% in 20 years**