

STANLEY

STANLEY FATMAX® LED Ratchet Screwdriver

FMHT0-62689



Features:

- Fine 45 tooth ratchet offering very high torque up to 3x human strength
- LED lights for easy working in dark areas
- Large soft grip handle with bit storage for added comfort and convenience
- 3 position ratchet enables clockwise, anti-clockwise and locked ratcheting positions
- FATMAX® Ratchet Screwdriver includes 12 bits
- Magnetic bit retention prevents bit loss

Description:

The STANLEY FATMAX® Ratchet Screwdriver Set features an integrated LED light which offers improved work piece lighting in darker areas. The fine 45 tooth ratchet offers very high torque that can deliver up to 3 times human strength for tightening, allowing you to complete the job quickly and effortlessly. Its large soft handle features bit storage, saving you time searching for bits. The three position ratchet enables clockwise, anti-clockwise and locked ratcheting positions for multiple applications.

Specifications	
Colour	Black/ Yellow
Handle Material	Bi-material
Screwdriver Bit Quantity	12
Tip Type	Flat, Phillips, Pozidriv, Torx
Tip Size	Flat: 5, 6.5 , 8 mm ; Phillips: PH1, PH2, PH3; Pozidriv: PZ1, PZ2, PZ3; Torx: T10, T15, T20