



Main

Range of product	DuoLine
Product or component type	Pushbutton
Device short name	BP'clic

Complementary

Contacts type and composition	1 NC
[Ie] rated operational current	20 A
[Ue] rated operational voltage	250 V AC
Control type	1 pushbutton grey
Light source	LED
Cap/Operator or lens colour	Red
Bulb lifespan	100000 H
Signalling circuit voltage	AC: 110...230 V 50/60 Hz
Power consumption	0.3 W
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Comb busbar distribution block compatibility	Upside: ProDis Upside: Bar'clic
9 mm pitches	2
Height	82 mm
Width	18 mm
Depth	71.5 mm
Colour	White
Electrical durability	AC-22: 30000 cycles AC 50/60 Hz
Connections - terminals	Staggered tunnel terminal 2 cable(s) 5 mm ² rigid without Staggered tunnel terminal 2 cable(s) 5 mm ² rigid with Staggered tunnel terminal 2 cable(s) 5 mm ² flexible without Staggered tunnel terminal 2 cable(s) 5 mm ² flexible with

Environment

Standards	IEC 60669-1 IEC 60947-5-1
Product certifications	NF

Contractual warranty

Period	18 months
--------	-----------