



## 40365 - OT\*Q50PAR20 240V E27 30DGR GE BX1/15

### • Specifications

#### General characteristics:

<b>Wattage [W]</b>	50
<b>Voltage [V]</b>	240
<b>Cap/Base</b>	E27
<b>Bulb Shape</b>	PAR
<b>Bulb Diameter [mm]</b>	64
<b>Colour temperature [K]</b>	2800
<b>Colour Rendering Index (CRI) [Ra]</b>	100
<b>Rated Life [h]</b>	2000
<b>Dimming Capability</b>	Yes
<b>Coil type</b>	CC-8
<b>Beam Angle [°]</b>	30
<b>Center Beam Candlepower [cd]</b>	1000
<b>Maximum Overall Length [mm]</b>	88
<b>DUN Code</b>	10043168403655
<b>EAN Code</b>	0043168403658
<b>Net weight per piece [g]</b>	107
<b>Gross weight per piece [g]</b>	155
<b>Pack Quantity</b>	15
<b>Layer quantity EUR (PC)</b>	135
<b>Layer quantity UK (PC)</b>	180
<b>Pallet quantity EUR (PC)</b>	945
<b>Pallet quantity UK (PC)</b>	1260
<b>Outer case size</b>	370 x 245 x 150 (mm)
<b>Energy Efficiency Class</b>	F
<b>Brand</b>	General Electric (GE)
<b>Product status</b>	Available