

Datasheet

RS Pro Coaxial Cable Assembly

RS Stock No: **546-2879**



Product Details

RS Pro coaxial cable assembly is terminated with brass RG-402 SMA connector plugs at each end. This assembly has a characteristic impedance of 50 Ω and SMA connector type.

Features and Benefits

- 250 mm high performance cable assembly
- SMA connector plugs
- 2.6 mm diameter flexible cable to 26 GHz

Specifications:

Cable Shape	Coaxial
Characteristic Impedance	50 Ω
Coaxial Type	RG402
Conductor Material	Brass
Connector A Gender	Male
Connector A Type	SMA
Connector A	Male SMA
Connector B Gender	Male
Connector B Type	SMA
Connector B	Male SMA
Insulation Material	PTFE
Length	250 mm
Maximum Operating Temperature	+85°C
Minimum Operating Temperature	-40°C
Operating Temperature Range	-40 to +85°C
Sheath Colour	Black
Standards Met	MIL-STD-348A
Voltage Rating	500 V